MICROMACHINED SILICON OF OMEGATION MODULAR PRESSURE SENSOR



Configurable—High Accuracy—High Temperature Performance For Industrial, Test and Measurement, and Aerospace Applications

Low Pressure from 10 in-H₂0 to 2.5 psi and Standard Ranges from 5 to 5000 psi Metric Ranges: 25 mbar to 350 bar

MM Series Pressure **Transducers**





- Customer Selectable Features
- ✓ Fast Delivery

on Custom Configuration

- ✓ High Accuracy
- ✓ Up to ±0.03% Linearity

Available Accuracies:

±0.05% FS BSL Accuracy

±0.08% FS BSL Accuracy

±0.20% FS BSL Accuracy

±0.40% FS BSL Accuracy

✓ Premium Temperature **Performance**



MMG10WVP3C1T2A2, features 0 to 10 in-H2O, output, 0.08% accuracy, twist-lock termination.

MMG100C1P5C6T3A3,

mini DIN termination.

features 100 psig

4 to 20 mA output, 0.40% accuracy,

All models shown actual size.

MMDWU015VP5C1T3A3, features 15 psid, mV output, 0.40% accuracy, twist-lock termination.

Note: BSL = Best Straight Line.

ONE SOURCE FOR ALL YOUR PRESSURE MEASUREMENT APPLICATIONS



○ OMEGA[™]

OMEGA has developed a rapid delivery system for its new Micro Machined Silicon product line.

You can have your pick of pressure ports, electrical connections, pressure range and units, thermal range and accuracy and accessories like trim pots. There are over 1-million possible combinations. OMEGA can deliver reasonable quantities of almost any combination within 5 working days. We have an easy-to-use configurator online at omega.com where you can select the transducer with the exact specifications for your project.

We also have the most popular configurations stocked for same day shipment!

OMEGA's micro-machined piezoresistive pressure transducers have a proven record in high performance commercial, automotive, test and measurement and aerospace applications. The piezoresistive process uses strain gages molecularly embedded into a highly stable silicon wafer. The silicon wafer is diced into individual die which each contain a full strain gage bridge. The die is mounted in a sealed chamber protected from the environment by glass to metal seals and a pressure sensitive stainless steel diaphragm. A small volume of silicone oil transfers the pressure from the diaphragm to the strain bridge. The construction provides a very rugged transducer with exceptional accuracy, stability and thermal effects.

A unique design ruggedizes the transducers by providing secondary fluid containment in the event of a diaphragm rupture.

- ✓ Five Accuracies
- ✓ Ninety-Two Pressure Ranges
- ✓ Ten Electrical Outputs
- ✓ Four Thermal Ranges
- ✓ Fourteen Pressure Ports
- ✓ Five Electrical Terminations
- Over 1,000,000 Combinations!

MM SERIES





CABLE CONNECTION			
COLOR	mV	5/10V	mA
BLACK	– EXC	Common	– EXC
WHITE	+ SIG	+ Out	+ CAL
GREEN	– SIG	SHUNT	SHUNT
RED	+ EXC	+ EXC	+ EXC

ANE	M12, MINI DIN AND SOLDER PINS CONNECTION			
PIN	mV	5/10V	mA	
1	+ EXC	+ EXC	+ Supply	
2	– EXC	Common	- Supply	
3	+ OUT	+ Output	NC	
4	– OUT	NC	NC	

TWIST-LOCK CONNECTION			
PIN	mV	5/10V	mA
Α	+ EXC	+ EXC	+ EXC
В	– EXC	Common	– EXC
С	+ OUT	+ OUT	+ SHUNT
D	- OUT	+ SHUNT	+ SHUNT
E	NC	NC	NC
F	NC	NC	NC

COMMON SPECIFICATIONS G/A/V/CG/BARO

Approvals: RoHS and CE

Calibration: 5-point NIST traceable Bandwidth: DC to 1 kHz typical Response Time: < 1 ms

CE Compliant: IEC61326 Emissions: IEC550022 Class B

Electrostatic Discharge Immunity: IEC1000-4-2

EM Field Immunity: IEC61000-4-3 EFT Immunity: IEC61000-4-4 Surge Immunity: IEC61000-4-5 Conducted RF: IEC61000-4-6

Rate Power Frequency Magnetic Field: IEC61000-4-8 Minimum Resistance Between Body and Any Wire:

100 MΩ @ 50 Vdc

Weight: 115 to 200 g (4 to 7 oz) (depending

upon configuration)
Environmental

Operating Temperature: -45 to 121°C (-49 to 250°F)

Protection:

Cable: 2 m (6') IP67 mini DIN: IP65

Twist-Lock and M12: IP65

Conduit 2 m (6') Cable with ½ NPT Conduit Fitting: IP67

Mechanical

Wetted Parts: 316L stainless steel Media: Compatible with 316L SS Pressure Cycles: 1 million minimum Long Term Stability (1-Year): ±0.1% FS typical

Shock: 50 g, 11 mS half sine, vertical and horizontal axis **Vibration:** 5-2000-5 Hz, 30 minute cycle, curve L, mil-spec

810 figure 514-2-2, vertical and horizontal axis

Overpressure Gage Pressure:

10-in H₂O: 10 times span

1 psi: 6 times span

2.5 psi to 3500 psi: 4 times span **5000 psi:** 15,000 psi max

Overpressure Absolute Pressure:

5 psia: 6 times span

2.5 psia to 3500 psia: 4 times span

5000 psia: 15000 psi max
Secondary Containment
Gage/Diff/Vac/Compound:
10 in-H₂O to 5 psi: To 1000 psi
15 to 1000 psi: To 3000 psi
1500 to 5000 psi: To 15,000 psi

Absolute/Barometric:

5 to 1000 psi: To 6000 psia **1500 to 5000 psi:** To 15,000 psia

Excitation

3 mV/V: 10 Vdc (ratiometric 5 to 10 Vdc) 10 mV/V: 10 Vdc (ratiometric 5 to 10 Vdc) 0 to 5 Vdc: 10 to 30 Vdc @ 10 mA

0 to 10 Vdc: 15 to 30 Vdc @ 10 mA

4 to 20 mA: 9 to 30 Vdc (9 to 20 Vdc above 229°F) **Bipolar Amplifiers:** Same as corresponding

outputs from above—compound and some differential

pressure models

MM SERIES SANITARY PROCESS SENSORS

○E OMEGA™

Using Micro-Machined Silicon Technology 10 mV/V. 0 to 5 Vdc. 4 to 20 mA Outputs


Gage Pressure: 10 inH₂0 to 600 psi (25 mb to 41 bar) Absolute Pressure: 5 to 600 psi (345 mb to 41 bar) Compound Gage: ±10 inH20 to ±15 psi (±25 mb to ±1 bar) Vacuum (Negative Gage): 0 to -10 inH₂0 to 0 to -15 psi

(25 mb to 1 bar)

Barometric Ranges: 0 to 32 inHg to 26 to 32 inHg

Sanitary Pressure Transducers and Transmitters





- ✓ Solid State Sensor for **Durability**
- ✓ Excellent Long Term **Stability**
- ✓ Welded Stainless Steel Construction
- ✓ 316L SS Wetted Parts
- Shock and Vibration Rated
- ✓ High Overpressure Rating
- Ruggedized with **Secondary Containment** System

The MM Series micro-machined silicon transducers with 1½ or 2" sanitary fittings are ideal for

(2.52)

PX429S20 2" flange


in food processing, beverage or bio/pharmaceutical applications as well as industrial applications that require a rugged, high accuracy transducer. The micro-machined silicon sensor provides a transducer with excellent long term stability. The modular construction allows for fast delivery of most configurations and fittings.


COMMON SPECIFICATIONS SANITARY

Accuracy: 0.4% to 0.05% best straight line (linearity, hysteresis and repeatability combined)

Note: bidirectional differential models calibrated in positive direction only

Calibration: 5-point NIST traceable calibration with zero and span values. calibrated in horizontal direction





PX419S20-100AV, shown smaller than actual size.

Span Setting: ±0.5% FS typical ±1% max (for ranges ≤2.5 psi ±1% typ. ±2% max)

Operating Temperature Range: -15 to 115°C (-5 to 240°F)

Compensated Temperature Range:

Ranges \leq 5 psi: 4.4 to 60°C (40 to 140°F)

Ranges > 5 psi: -4 to 85°C (25 to 185°F)

Temperature Compensation: Zero and Span Shift Over Compensated Range

Ranges ≤ 25 psi: **Zero:** 1.00% Span: 0.70% Range = 5 psi: **Zero:** 0.80% **Span:** 0.50%

Ranges > 5psi: **Zero:** 0.50% **Span:** 0.50%

26B & 26HB Barometric Range:

Zero: 0.90% **Span:** 0.50%

Minimum Isolation Between Case and **Output Terminations:**

100M Ω @ 50 Vdc

Pressure Cycles: 1 million, min Long Term Stability (1-Year): ±0.1%

FS typ.

Shock: 50 g, 11 mS half sine shock,

(under test)

Vibration: ±20 g (under test) Bandwidth: DC to 1 kHz typical Response Time: <1 mS

Fill Fluid: NEOBEE M5 food grade

(1.98)

PX419S15 11/2" flange

MM SERIES SANITARY PROCESS SENSORS



High Accuracy Pressure Transducers Piezoresistive Design With High Temperature Performance

All images shown smaller than actual size.



PX409 Cable Connection				
Color	mV	5/10V	mA	
Black	– EXC	Common	Supply	
White	+ SIG	+ Output	NC	
Green	– SIG	NC	NC	
Red	+ EXC	+ EXC	+ Supply	




PX419/PX459 Pinout			
Pin	mV	5/10V	mA
1	+ EXC	+ EXC	+ Supply
2	– EXC	Common	- Supply
3	+ SIG	+ Output	NC
4	– SIG	NC	NC



PX429 Twist-Lock Pinout			
Pin	mV	5/10V	mA
Α	+ EXC	+ EXC	+ Supply
В	– EXC	Common	- Supply
С	+ SIG	+ Output	NC
D	– SIG	NC	NC
Е	NC	NC	NC
F	NC	NC	NC

NC = No Connection.



Approved to 3A Sanitary Specification 74-03

CE Compliant: Meets industrial emissions and immunity standard IEC61326 for industrial locations

Environmental Protection:

IP65 or IP67 depending upon electrical termination

Pressure Rating:

½ and 2" Tri-Grip™ (compatible with Tri-Clamp®)

Fitting: 600 psi using suitable clamp **Over Pressure:** 4 x rated pressure to maximum rated flange pressure

Secondary Containment: 6 x rated pressure to a maximum of 2000 psi

(not in clamp)

Wetted Parts: 316L SS Weight: 285 g (10 oz)

OUTPUT SPECIFICATIONS

Specifications (mV/V Output)
Output: 10 mV/V: ratiometric

5 to 10 Vdc

Supply: 5 to 10 Vdc

Specifications (Amplified Voltage Output)

Output/Supply:

0 to 5 Vdc: 10 to 30 Vdc **0 to 10 Vdc**: 15 to 30 Vdc

Specifications (4 to 20 mA Output) Output/Supply:

Output: 4 to 20 mAdc

Supply: 9 to 30 Vdc [9 to 20 Vdc above 105°C (229°F)] max loop res $\Omega = \text{(Vs-9)} \times 50$

MM SERIES SANITARY PROCESS SENSORS **USB OUTPUT**



USB Output Sanitary Fitting Pressure Transducer

Connect Directly to Your PC or Lapton

Gage, Absolute, Compound Gage, Vacuum and Barometric Pressures 10 inH₂0 to 600 psi (25 mb to 41 bar)

MM Sanitary USB Series



USB SANITARY SPECIFICATIONS

Accuracy: 0.08% typical best straight line, 0.14% max (linearity, hysteresis and repeatability combined) compound gage models calibrated in positive direction only

Calibration: 5-point NIST traceable calibration with zero and span values calibrated in horizontal direction

Zero Balance: ±0.5% FS typical ±1% max (for ranges ≤2.5 psi ±1% typical ±2% max)

Span Setting: ±0.5% FS typical ±1% max (for ranges ≤2.5 psi ±1% typical ±2% max)

Operating Temperature Range: -15 to 95°C (-5 to 203°F)

Compensated Temperature Range:

Ranges ≤ **5 psi**: 4.4 to 60°C (40 to 140°F)

Ranges > 5 psi: -4 to 85°C

(25 to 185°F) Temperature Compensation

Zero and Span Shift Over Compensated Range: Ranges ≤2.5 psi:

Zero: 1.00% Span: 0.70% Range = 5 psi: **Zero:** 0.80% **Span:** 0.50%

Ranges > 5psi:

Zero: 0.50% **Span:** 0.50%

26B/26HB Barometric Range:

Zero: 0.90% Span: 0.50%

Minimum Isolation Between Case and **Output Terminations:**

100M Ω @ 50 Vdc

Pressure Cycles: 250,000, minimum Long Term Stability (1-Year): ±0.1%

FS typical

Shock: 50 g, 11 mS half sine shock,

(under test)

Vibration: ±20 g (under test) Bandwidth: DC to 3 Hz typical A to D Conversion: 14 bit Response Time: <1 mS

Fill Fluid: NEOBEE M5 food grade

Approved to 3A Sanitary Specification 74-03

CE Compliant: Meets industrial emissions and immunity standard

IEC61326

Environmental Protection: IP65


Pressure Rating: ½ and 2" Tri-Grip™

Fitting: 600 psi using suitable clamp Over Pressure: 4 x rated pressure to maximum rated flange pressure Secondary Containment: 6 x rated

pressure to a maximum of 2000 psi (not

in clamp)


Wetted Parts: 316L SS Weight: 285 g (10 oz)





FREE SOFTWARE INCLUDED!

Each unit includes free software that converts your PC into a strip chart recorder or data logger so readings can be saved and later printed or exported to a spread sheet file. Also included are software drivers for some of the most popular Laboratory programs.



MM SERIES DIFFERENTIAL PRESSURE MODELS



mV/V, 0 to 5 or 0 to 10 Vdc, or 4 to 20 mA Outputs Uni-Directional or Bi- Directional 0-10 inH₂0 to 0-1000 psid

MM Series



- Precision Micro-Machined Silicon Core
- ✓ 5-Point NIST Traceable **Calibration**
- High Stability, Low Drift
- Welded Stainless Steel Construction
- ✓ 316L SS Wetted Parts
- ✓ Premium Temperature **Performance**
- Broad Compensated **Temperature Range**
- ✓ Durable, 1 Million Cycle Life
- Ruggedized with **Secondary Containment**
- Customized Specifications Available

COMMON SPECIFICATIONS DIFFERENTIAL

Accuracy: 0.4% to 0.05% best straight line (linearity, hysteresis and repeatability combined)

Note: bidirectional differential models calibrated in positive direction only

Minimum Resistance Between **Transducer Body**

and Any Wire: 100 MΩ **Operating Temperature:**

mV/V and 5 to 10 Vdc Output:

-45 to 121°C (-49 to 250°F) mA Output: -45 to 115°C

(-49 to 239°F)

Compensated Temperature Range:

10 inH₂O to 5 psi: -17 to 85°C

(1 to 185°F)

15 to 1000 psi: -29 to 85°C

(-20 to 185°F)

Thermal Accuracy:

% Span Shift over compensated temperature range

Span Zero 10 inH₂O to 1 psi: ±1.00% ±1.00%

2.5 to 1000 psi: ±0.50% ±0.50

Pressure Cycles: 1 million minimum

Long Term Stability (1-Year):

±0.1% FS typical

Bandwidth: DC to 1 kHz typical

Response Time: <1 ms

CE Complient: Meets EN1326-1:

2006 for industrial locations

Shock: 50 g, 11 mS half sine, vertical and horizontal axis

Vibration: 5-2000-5 Hz, 30 minute cycle, Curve L, Mil-Spec 810 figure 514-2-2, vertical and horizontal axis

Wetted Parts: 316L stainless steel

Wet Dry:

Positive Side: 316L stainless steel Negative Side: Clean, dry, non-ionic

Line/Static Pressure: 500 psi max applied to both sides simultaneously

Proof Pressure (Differential):

10 in H_2O range = 10 times range 1 psi range = 6 times range 2.5 to 750 psi ranges = 4 times range 1000 psi range = 3 times range

Hi Side Containment Pressure (Differential):

Ranges 10 inH2O to 5 psi: to 1000 psi Ranges 15 to 1000 psi: to 3000 psi

Pressure Ports: Select **Electrical Terminations:** PX409: 2 m (6') cable

PX409C: 2 m (6') cable with ½ NPT

conduit thread PX419: mini DIN


(mating connector included)

PX429: Twist-lock,

(mating connector sold separately)


PX459: M12 connector PX429 Mating Connector: PT06F10-6S


Weight: 200 g (7 oz) max





ELECTRICAL TERMINATION


















DIMENSIONS










PRESSURE PORTS*

Ø = diameter Dimensions: mm (inch)



^{*} Dimensions may vary slightly for ranges >1000 psi.