

# SERIES 2-5000 | MINIHELIC® II DIFFERENTIAL PRESSURE GAGE



#### **FEATURES/BENEFITS**

- · Removable lens and rear-housing provides easy, cost-effective servicing
- Accuracy and value provides an excellent solution for OEM and user applications
- · Durable housing materials make it well-suited for rough environments and total high pressure

## **APPLICATIONS**


- · Room positive pressure sensing
- Cabinet air-purging
- Medical respiratory equipment
- Air samplers
- · Electronic air cooling systems
- · Laminar flow hoods
- · Local indication on filter status
- Face velocity on fume hood
- Duct pressures

## **DESCRIPTION**

Combining clean design, small size and low cost with enough accuracy for all but the most demanding applications our **Series 2-5000 Minihelic® II Gage** offers the latest in design features for a dial type differential pressure gage. It is our most compact gage but is easy to read and can safely operate at total pressures up to 30 psig.

## **SPECIFICATIONS**

Service	Air and compatible gases.
Wetted Materials	Consult factory.
Housing	Glass filled nylon; polycarbonate lens.
Accuracy	±5% of FS at 70°F (21.1°C).
Pressure Limits	30 psig (2.067 bar) continuous to either pressure connection.
Temperature Limits	20 to 120°F (-6.67 to 48.9°C).
Mounting Orientation	Diaphragm in vertical position. Consult factory for other position orientations.
Process Connections	Barbed, for 3/16" ID tubing (standard); 1/8" male NPT (optional).
Weight	6 oz (170.1g).
Agency Approvals	Meets the technical requirements of EU Directive 2011/65/EU (RoHS II)
Caution: FOR USE ONLY WITH AIR OR COMPATIBLE NON-CORROSIVE GASES	



## **HOW TO ORDER**

Use the **bold** characters from the chart below to construct a product code.



#### SERIES/RANGE -

2-5000-0: 0 to 0.5 in w.c 2-5001: 0 to 1 in w.c 2-5002: 0 to 2 in w.c 2-5003: 0 to 3 in w.c 2-5005: 0 to 5 in w.c 2-5205: 0 to 5 psid 2-5210: 0 to 10 psid 2-5000-125PA: 0 to 125 Pa 2-5000-250PA: 0 to 250 Pa 2-5000-500PA: 0 to 500 Pa 2-5000-750PA: 0 to 750 Pa

## -AT: Aluminum tag

-BB: Bottom barb connection -FC: Factory calibration

-NIST: NIST traceable calibration certificate

-NPT: NPT connection

#### **ACCESSORIES**

Model	Description
A-434	Portable kit for Series 2-5000 Minihelic® II gage
A-609	Air filter kit for Series 2-5000 Minihelic® II gage
A-497	Mounting bracket for the Series 2-5000 Minihelic® II differential pressure gage
A-489	4" 303 SS straight static pressure tip with flange
A-362	Stand-hang bracket, aluminum, for Minihelic® II gage

## **ORDER ONLINE TODAY!**

dwyer-inst.com/Product/Series2-5000



DWYER INSTRUMENTS, INC.

©Copyright 2019 Dwyer Instruments, Inc. Printed in U.S.A. 11/19

DS-2-5000 Rev. 1