FLOW METER PROCESSCOMEGACONTROL INFORMATION SYSTEMS



FLR Flow Sensors

- ✓ 2% FS Accuracy
- No Straight Pipe Run Required
- Mounts in Any Position
- 4 to 20 mA,
 0 to 5 Vdc, and
 0 to 10 Vdc
 Standard Outputs
- Digital Flow Rate and Total Flow Indicator
- In-Field Compensation for:
 - Specific Gravity of All Fluids
 - Viscosity of
 - Petroleum-Based Fluids – Specific Gravity,
 - Pressure, and Temperature of Pneumatic Applications



Rugged In-Line Flow Sensors

Available in 13 mm $(\frac{1}{2}^{"})$, 19 mm $(\frac{3}{4}^{"})$, and 32 mm $(1\frac{1}{4}^{"})$ sizes with anodized aluminum or brass. Comes with 4.5 m (15') of stripped end integral cable. In the field, integral cable can be extended up to 300 m (1000') with shielded copper cable. Units are securely

protected in a sturdy cast aluminum enclosure, and are easy to install and mount in any position, vertical or horizontal. Capable of monitoring fluids to 150 GPM or pneumatic lines to 1000 SCFM.

SPECIFICATIONS

Temperature Range: -29 to 116°C (-20 to 240°F) Maximum Pressure: 3500 psig (liquids); 1000 psig (gases)

Power Requirement:

0 to 5 Vdc Output: 10 to 30 Vdc @ 0.75 W maximum 0 to 10 Vdc Output: 12 to 30 Vdc @ 0.75 W maximum

4 to 20 mA Output: Loop-powered, 30 Vdc maximum

Power Consumption: 25 mA maximum Circuit Protection:

Reverse polarity and current limit **Repeatability:** ±0.5%

Non-Linearity: ±0.05%

Isolation: Inherently isolated from the piping system

Display: Fixed or toggle modes of operation for rate and totalizer display. 8-digit, 0.70" high numeric display for rate and total 8-digit 0.35" high alphanumeric display for units and setup

Response Time: 1.0 sec

Temperature Drift:

0.05% of span per °C maximum

Dimensions: mm (inch)

Analog Outputs:

4 to 20 mA into $1K\Omega$ maximum 0 to 5 Vdc into $10K\Omega$ minimum 0 to 10 Vdc into $10K\Omega$ minimum User Connections:

15' pig-tail (standard) Transmission Distance:

4 to 20 mA limited by cable resistance 0 to 5 Vdc 300 m (1000') maximum 0 to 10 Vdc 300 m (1000') maximum **Enclosure:**

Material: Anodized and epoxy powder-coated aluminum with polycarbonate lens Seals: Silicone gasket between

enclosure and lens/cover FKM O-rings between enclosure and flow meter body


Connection: 4-pin connection (standard)


Fasteners: T303 SS


Rating: NEMA 12 and 13 (IP52/54) Materials:

2024 - T351 anodized aluminum body, piston and cone C360 brass body, piston and cone petroleum (oil) common parts Spider Plate: T316 SS Spring: T302 SS Fasteners: T303 SS Pressure Seals: FKM Lens: Polycarbonate Retaining Ring: SAE 1070/1090 carbon steel Retaining Spring: SAE 1070/1090 carbon steel Internal Magnet: PPS/ceramic Enclosure Seal: Silicone gasket water-based, water, air common parts Spider Plate: T316 SS Spring: T302 SS Fasteners: T303 SS Pressure Seals: FKM Lens: Polycarbonate Retaining Ring: T316 SS Retaining Spring: ST316 SS Internal Magnet: PPS/ceramic Enclosure Seal: Silicone gasket

| | В | С | D | Е | F | G | Н | I | J | К |
|-----------------------------|---------|---------|---------|--------|--------|--------|--------|--------|--------|-----------|
| Nominal Port Size | Length | Length | Length | Width | Width | Width | Width | Depth | Offset | Hole Dia. |
| (SAE 6) | 168 | 134 | 163 | 152 | 82 | 76 | 107 | 75 | 38 | 8 |
| | (6.60) | (5.27) | (6.41) | (6.00) | (3.23) | (3.00) | (4.20) | (2.94) | (1.51) | (0.31) |
| (SAE 6) | 168 | 134 | 163 | 152 | 82 | 76 | 107 | 75 | 38 | 8 |
| | (6.60) | (5.27) | (6.41) | (6.00) | (3.23) | (3.00) | (4.20) | (2.94) | (1.51) | (0.31) |
| ³ / ₄ | 183 | 134 | 179 | 152 | 91 | 76 | 107 | 75 | 32 | 8 |
| (SAE 6) | (7.20) | (5.27) | (7.04) | (6.00) | (3.60) | (3.00) | (4.20) | (2.94) | (1.27) | (0.31) |
| 1 | 183 | 134 | 179 | 152 | 91 | 76 | 107 | 75 | 32 | 8 |
| (SAE 6) | (7.20) | (5.27) | (7.04) | (6.00) | (3.60) | (3.00) | (4.20) | (2.94) | (1.27) | (0.31) |
| 1¼ | 310 | 271 | 296 | 194 | 123 | 97 | 128 | 114 | 56 | 8 |
| (SAE 6) | (12.20) | (10.68) | (11.65) | (7.63) | (4.84) | (3.82) | (5.02) | (4.50) | (2.20) | (0.31) |
| 1½ | 310 | 271 | 296 | 194 | 123 | 97 | 128 | 114 | 56 | 8 |
| (SAE 6) | (12.20) | (10.68) | (11.65) | (7.63) | (4.84) | (3.82) | (5.02) | (4.50) | (2.20) | (0.31) |









| To Order | | | | |
|-----------|------------------|-------------|--------------|----------|
| Model No. | Flow Range | Medium | NPT | Body |
| FLR6102D | 0.2 to 2.0 GPM | Oil | 1/2 | Aluminum |
| FLR6105D | 0.5 to 5.0 GPM | Oil | 1/2 | Aluminum |
| FLR6115D | 1 to 15 GPM | Oil | 1/2 | Aluminum |
| FLR7120D | 2 to 20 GPM | Oil | 3⁄4 | Aluminum |
| FLR7130D | 3 to 30 GPM | Oil | 3⁄4 | Aluminum |
| FLR8140D | 4 to 40 GPM | Oil | 1 | Aluminum |
| FLR8150D | 5 to 50 GPM | Oil | 1 | Aluminum |
| FLR9175D | 10 to 75 GPM | Oil | 1 ¼ | Aluminum |
| FLR9110D | 10 to 100 GPM | Oil | 1 1⁄4 | Aluminum |
| FLR9115D | 10 to 150 GPM | Oil | 1 1⁄4 | Aluminum |
| FLR6302D | 0.2 to 2.0 GPM | Water | 1/2 | Brass |
| FLR6305D | 0.5 to 5.0 GPM | Water | 1/2 | Brass |
| FLR6315D | 1 to 15 GPM | Water | 1/2 | Brass |
| FLR7320D | 2 to 20 GPM | Water | 3⁄4 | Brass |
| FLR7330D | 3 to 30 GPM | Water | 3⁄4 | Brass |
| FLR8340D | 4 to 40 GPM | Water | 1 | Brass |
| FLR8350D | 5 to 50 GPM | Water | 1 | Brass |
| FLR9375D | 10 to 75 GPM | Water | 1 ¼ | Brass |
| FLR9310D | 10 to 100 GPM | Water | 11⁄4 | Brass |
| FLR9315D | 10 to 150 GPM | Water | 11⁄4 | Brass |
| FLR6725D | 2 to 25 SCFM | Air 100 psi | 1/2 | Aluminum |
| FLR6750D | 5 to 50 SCFM | Air 100 psi | 1/2 | Aluminum |
| FLR7710D | 10 to 100 SCFM | Air 100 psi | 3⁄4 | Aluminum |
| FLR7715D | 15 to 150 SCFM | Air 100 psi | 3⁄4 | Aluminum |
| FLR8725D | 25 to 250 SCFM | Air 100 psi | 1 | Aluminum |
| FLR9740D | 25 to 400 SCFM | Air 100 psi | 1 1⁄4 | Aluminum |
| FLR9760D | 50 to 600 SCFM | Air 100 psi | 1 1⁄4 | Aluminum |
| FLR9710D | 100 to 1000 SCFM | Air 100 psi | 11⁄4 | Aluminum |

Comes complete with operator's manual.

For 5-point NIST certificate add "-NIST5" to model number for additional cost.

For British standard pipe thread parallel add "-BSPP" to model number, no additional cost.

Ordering Examples: FLR6105D, flow transmitter, 0.5 to 5.0 GPM for oil, with analog output FLR5101D, flow transmitter, 0.1 to 1.0 GPM for oil with analog output.