

Temperature/Relative Humidity Data Logger with Display

Part of the NOMAD Family

OM-DVTH



- ✓ **Text Display Shows:**
Real Time Temperature, Humidity and Dew Point; Logging Summary, Sample Rate, Memory Used and Memory Left
- ✓ **Graph Display Shows:**
Measurement Trends Graphically, with Scrolling Feature
- ✓ **Visual Over and Under Alarm Indicators** for Temperature and Humidity
- ✓ **USB Connection**
- ✓ **Compatible with Windows® XP/VISTA/7/8**
- ✓ **Calibration Through Software**
- ✓ **Ideal for Refrigerators, Freezers, Museums, Computer Rooms, Labs**

The OM-DVTH temperature/relative humidity data logger with display is an easy-to-use, versatile device which can be used for a wide range of logging applications. The OM-DVTH records and instantly displays trends for temperature, humidity and dew point. With the OM-DVTH you can monitor real time measurements for instant environmental conditions. When you're ready, download over 40,000 data points to your PC for further analysis. Data logging has never been this visual. The OM-DVTH is capable of sampling as fast as once per second or as slow as every 18 hours. A total of 43,344 temperature measurements can be stored in the data logger memory if only



OM-DVTH shown larger than actual size.

temperature is measured, or 21,672 measurements for temperature, humidity and dew point if all three parameters are measured.

Easy-to-use Windows software is included with the OM-DVTH. The software is a full-featured program that allows you to set up all data logger functions including sampling rate, logging duration, start mode, logging mode, and high and low temperature and relative humidity alarm values. Once data has been logged, the program then allows you to download data from the logger, plot the data and export the data to an ASCII text or Excel® file format for further analysis.

Specifications

LOGGER

Text Display: Displays real time temperature, humidity and dew point; also displays logging summary, sample rate, memory used and memory left

Graph Display: Shows measurement trends graphically; graph can be scrolled through the entire logged data

Sample Point Capacity:

43,344 points for temperature only; 21,672 points for temperature, humidity and dew point

Alarms: Visual over and under alarm indicator for temperature and humidity (dew point alarms are not available)

Calibration: User single point offset calibration is available through software for both temperature and humidity; calibration is password protected

Operating Temperature:

-10 to 65°C (15 to 150°F)

Temperature Accuracy:

±0.5°C (±1°F)

Temperature Resolution: 0.01°C (0.01°F)

Relative Humidity Range:

0 to 99% RH, non-condensing

Relative Humidity Accuracy:

±2% RH, from 10 to 90% RH

Relative Humidity Resolution:

0.01% RH

Time Accuracy: ±100 ppm @ 75°F

Display:

LCD

Storage Temperature:


-20 to 70°C

(-5 to 160°F)

Dimensions:

7.7 H x 10.2 W x 3.8 cm D

(3.05 x 4 x 1.5")



Windows software displays data in graphical or tabular format.

Weight: 200 g (7.0 oz)
Power: 3 "AA" alkaline or lithium batteries (included)
Battery Life: 2 years (average use)

SOFTWARE

PC Interface: USB port (USB cable is included)
Sampling Interval: User selectable from 1 second to 18 hours, in 1 second increments
Data Security: Unique factory set logger ID; recording session counter; password protected calibration

Operating System Compatibility: Windows XP/VISTA/7/8 (32- and 64-bit)

Minimum System Requirements: 5 MB of free disk space, 800 x 600 screen resolution, 1 free USB port

Recording Start: On button press, immediate after setup, or at a user specified date and time

Recording Mode: Stop on memory full, or continuous recording with memory rollover

Real Time Status: Visual indication through the status LED; software real time status

User Calibration: Password protected calibration for each channel

User Information: Up to 30 characters

Logger Channels: User selectable; disabling channels increases the storage capacity of the other channels

Units: US and metric

Data Format: Exportable to text or Excel files



OMEGACARESM extended warranty program is available for models shown on this page. Ask your sales representative for full details when placing an order. OMEGACARESM covers parts, labor and equivalent loaners.

To Order	
Model No.	Description
OM-DVTH	Temperature/relative humidity data logger with display
OM-DVTH-CAL-3-HU	OM-DVTH temperature/humidity data logger with NIST traceable calibration certificate

Comes complete with operator's manual, Windows software on CD-ROM, 1.8 m (6') USB interface cable and 3 "AA" alkaline or lithium batteries.

Ordering Example: OM-DVTH, temperature/relative humidity data logger with display and OCW-1, OMEGACARESM extends standard 1 year warranty to a total of 2 years.