



CE OMEGA® User's Guide

Shop online at omega.com^{sм}

e-mail: info@omega.com For latest product manuals: www.omegamanual.info



FPR300/310 SERIES Low-Flow Meter



omega.com info@omega.com

Servicing North America:

U.S.A. Headquarters:

Omega Engineering, Inc.

Toll-Free: 1-800-826-6342 (USA & Canada only)

Customer Service: 1-800-622-2378 (USA & Canada only) Engineering Service: 1-800-872-9436 (USA & Canada only)

Tel: (203) 359-1660 Fax: (203) 359-7700

e-mail: info@omega.com

For Other Locations Visit omega.com/worldwide

General Information

| Features Specifications Dimensions Flow Range | Page 4 Page 4 Page 5 Page 5 Page 5 Page 5 |
|---|---|
| Installation & Connections | · · |
| K-Factor | Page 6Page 6 |
| Repair | |
| Sensor Replacement | Page 7Page 7Page 7Page 7Page 8 |
| Troubleshooting | |
| Probably Causes | Page 9Page 9 |

These versatile impeller flowmeters are available in 3/8", 1/2", 3/4", and 1" nominal pipe sizes with female NPT threads. They employ jewel bearings to allow for very low minimum flow rates and superior life.

The **FPR300**, with a body of polypropylene, is an economical choice for metering water or low corrosion fluids. The lens cover is available in a choice of materials: acrylic for visual when more corrosion resistance is needed. The standard 1000-MAW may be used for blind 4-20 mA transmission. rotor assembly is PVDF with tungsten carbide shaft. The O-ring is EPDM.

The **FPR310** offers greater chemical resistance with a PTFE body and cover, PTFE-coated FKM O-ring, and standard PVDF/ceramic rotor assembly.

The pulse output of these meters is compatible with many different types of controls, including a full range of Omega rate displays and controls. The Omega DPF-143 and DPF-144 provide flow rate and total flow indication. The flow indication of low-corrosion fluids; polypropylene DPF-144 also includes 4-20 mA output capability. The FMG-

Features 18' Sensor Cable _____ Thread-in Sensor, Field Replaceable, ___ 6-24 Vdc Pulse Standard Acrylic Top with Clear Removable Lens Assembly . (optional polypropylene top without clear lens) Hex Screws __ Female NPT Ports _____ Polyproylene Body — <u>Internal</u> **FPR300** • Jewel Bearings—Ruby Ring and Ball PVDF/Tungsten Carbide Rotor Assembly (PVDF/Ceramic or PVDF/Silicon Carbide optional) • EPDM O-Ring (FKM or PTFE-coated FKM optional) 18' Sensor Cable _ Thread-in Sensor, Field Replaceable, _____ 6-24 Vdc Pulse PTFE Body and Top Screws with Hex Nuts -Female NPT Ports -Internal • Jewel Bearings—Ruby Ring and Ball • PVDF/Ceramic Rotor Assembly (PVDF/Silicon Carbide optional) • PTFE-coated FKM O-Ring (FKM or EPDM optional)

Page 4 omega.com


FPR310

Specifications*

| | | FPR300 | FPR310 | |
|------------------|------------|---|--|--|
| Connection Ports | | 3/8", 1/2", 3/4", 1" —Female NPT thread | 3/8", 1/2", 3/4", 1" —Female NPT thread | |
| Sensor Cable | 2 | 18 ft (6 m) standard—maximum cable run 2000 ft (607 m) | 18 ft (6 m) standard—maximum cable run 2000 ft (607 m) | |
| Materials | Body | Polypropylene | PTFE | |
| | Rotor | PVDF—2 magnet (6 magnet high resolution optional) | PVDF—2 magnet (6 magnet high resolution optional) | |
| | Shaft | Nickel tungsten carbide (ceramic or silicon carbide optional) | Zirconia ceramic (silicon carbide optional) | |
| | O-Ring | EDPM (FKM or PTFE-coated FKM optional) | PTFE-coated FKM (FKM or EDPM optional) | |
| | Bearings | Ruby ring and ball | Ruby ring and ball | |
| | Cover | Acrylic with clear lens (polypropylene without clear lens optional) | PTFE | |
| Maximum Te | emperature | 160° F (70° C) | 180° F (82° C) | |
| Maximum Pressure | | 150 psi (10 bar) | 150 psi (10 bar) | |
| Accuracy | | ±1% of full scale | ±1% of full scale | |
| Power | | 6–36 Vdc, 2 mA min. | 6–36 Vdc, 2 mA min. | |
| Outputs | | Current sinking pulse, 6–24 Vdc | Current sinking pulse, 6–24 Vdc | |

^{*} Specifications subject to change. Please consult our website for current data (omega.com)

Dimensions




| Model # | NPT Thread Size |
|---------|-----------------|
| -038 | 3/8" |
| -050 | 1/2" |
| -075 | 3/4" |
| -100 | 1" |

Flow Range

| Model # | K-Factor* (pulses/gal) | | Gal/Min | Liter/Min |
|---------|------------------------|--------|----------|-------------|
| | FPR310 | FPR300 | Gai/Wiln | Liter/wiiii |
| -038 | 1394 | 1417 | 0.07-5 | 0.27-18.9 |
| -050 | 634 | 658 | 0.1–10 | 0.38-37.9 |
| -075 | 476 | 468 | 0.2–20 | 0.75–75 |
| -100 | 250 | 254 | 0.5–40 | 1.9-150 |

*Nominal K-factors (based on averages) for standard 2-magnet FPR310 and FPR300. High resolution (6-magnet) K-factors are approximately tripled.

Pressure Drop Curves



INSTALLATION

Piping Requirements

Standard fittings are female NPT. If the piping connected to the meter is metallic, care should be taken not to overtighten. Straight pipe of at least five diameters upstream of the meter is recommended. Vertical or horizontal installations are acceptable.



WARNING:

This meter has low-friction bearings. Do not at any time test operation of the meter with compressed air. Doing so will subject it to rotational speeds many times those for which it was designed, and will certainly damage the rotor, shaft, and/or bearings.

K-Factor

The meter is factory calibrated. The K-factor is found on the label on the meter body and must be input into the control/display for accurate reading.




CONNECTIONS

Connecting to Control Devices


It is often desirable to connect an FPR300/310 flow sensor to a PLC or industrial computer board, and the sensors are well suited for this. Typically it can be connected directly, or with a single resistor added. The pickup sensors are current sinking (NPN) GMR devices that require 6–36 Volts DC and 2 mA current. They can connect directly to a PLC or computer board if:

- 1. The sensor power supply on the PLC is 6–36 Vdc (24 Vdc is typical).
- 2. The sensor power supply can provide at least 2 mA (100 mA is typical).
- 3. The sensor input on the PLC can accept a current sinking device.
- 4. The PLC frequency response > flow meter output frequency.



Input designed for current sinking devices (NPN)

If the PLC input only accepts current sourcing devices, a pull-up resistor must be added. Typically, on a 24 Vdc input a 2.2 K Ohm resistor will be effective.



Input designed for current sourcing (PNP) devices

Since the three-wire pickup sensors are solid state, they do not exhibit switch bounce and can be used at relatively high frequencies.

If the PLC is equipped with a 4-20 mA analog input module, it is necessary to order the FPR300/310 Series flow sensor with some form of 4-20 mA transmitter. Two options are the FMG-1000-MAW blind transmitter and the DPF144 indicating transmitter. Follow the connection diagrams for these products to connect to the analog input.

Page 6 omega.com

Rotor Replacement

There is only one moving part to this meter. The bearings are made of ruby, which rarely wears out or needs replacement unless they have been physically damaged by severe shock. The shaft is integrally molded into the rotor, and shaft and rotor are replaced as one part. (You may wish to replace the bearings, using the bearing removal tool, while the meter is disassembled for rotor replacement). To replace the rotor, disconnect the meter and remove the four screws that hold the cover in place. Lift the cover and remove the rotor (see parts diagram below).


When putting in the new rotor, be sure that the ends of the shaft are in both bearings before tightening the cover. The rotor can be easily dropped into the bottom bearing. Starting the shaft into the upper bearing requires a bit of care. It is easier if the rotor is spinning, which can be done by lightly blowing into a port. When the upper bearing plate drops into place, hold it down and check for free spinning (by blowing lightly) before replacing the cover. Check that the O-ring is in its seat on the bearing plate before replacing the cover. Replace the cover, insert the four cap screws and tighten.

Sensor Replacement

The sensor ordinarily does not need replacement unless it is electrically damaged. If replacement is necessary, unscrew the sensor by hand. Screw the replacement sensor in and tighten by hand.




Reconnect the sensor according to the diagram below.



Page 7 omega.com

FPR300/310 Parts List



| | | | FPR300 | FPR310 |
|---|-----------|---|-------------------|-------------------|
| 1 | Body | -038 | 100221 | 100269 |
| | | -050 | 100222 | 100268 |
| | | -075 | 100223 | 100267 |
| | | -100 | 100224 | 100266 |
| 2 | Flow dire | ection Label | 100256 | 100256 |
| 3 | Bearing A | Assembly (includes 2) | 103313 | 103313 |
| | Bearing I | Removal Tool (not shown) | 100372 | 100372 |
| 4 | Rotor wit | th Shaft | | |
| | | PVDF/Ceramic (2 magnet) | 103930 | 103930 |
| | | PVDF/Carbide (2 magnet) | 103931 | n/a |
| | | PVDF/Silicon Carbide (2 magnet) | 103933 | 103933 |
| | | PVDF/Ceramic (6 magnet, high res) | 100453 | 100453 |
| | | PVDF/Carbide (6 magnet, high res) | 103932 | n/a |
| | | PVDF/Silicon Carbide (6 magnet, high res) | 103934 | 103934 |
| 5 | O- Ring | EPDM | 100264 (standard) | 100264 (optional) |
| | | FKM | 100219 (optional) | 100219 (optional) |
| | | PTFE-coated FKM | 100973 (optional) | 100973 (standard) |
| 6 | Cover (af | ter 5/2005) | | |
| | | Polypro | 100849 | Not available |
| | | Acrylic | 100848 | Not available |
| | | PTFE | Not available | 100847 |
| 7 | Cover Sc | rews (4 required) | | |
| | | Hexscrew | 100310 | Not applicable |
| | | Screw (requires hex nut 100025) | Not applicable | 100022 |
| | | Hex nut (requires screw 100022) | Not applicable | 100025 |
| 8 | Sensor | | 100419 | 100419 |

Page 8 omega.com

| Probable Cause | Things to Try |
|--|---|
| Insufficient flow | Consult Flow Rate Chart Reduce pipe size or use different sensor |
| Bad connections to control electronics | Check connections at control: Red (+), Black (-), White (signal) |
| Incompatible control | Use 6–36 Vdc power supply Add pull up resistor, if using current-sourcing device |
| Damaged or missing rotor | Remove flow sensor from fitting and check for free spinning; replace rotor |
| Failed magnetic sensor | Replace magnetic sensor |
| Not enough straight pipe between meter and severe flow disturbance | Move meter away from flow disturbance or field calibrate |
| Wrong K-Factory entered | Check fitting for K-Factor, check indicator to see if it is entered properly ("Set K" on DPF143/144) |
| Magnetic sensor failing to pick up each blade | Remove flow sensor from pipe. If indicator is DPF143/144, set K to 1.00, turn rotor slowly by hand, indicator should count each blade; replace sensor |
| Wrong time units on flow indicator | If using DPF143/144, check left side of display (sec, min, hr, day); change to desired unit |
| | Insufficient flow Bad connections to control electronics Incompatible control Damaged or missing rotor Failed magnetic sensor Not enough straight pipe between meter and severe flow disturbance Wrong K-Factory entered Magnetic sensor failing to pick up each blade Wrong time units on flow |

Page 9 omega.com

Page 10 omega.com

OMEGA ENGINEERING, INC. warrants this unit to be free of defects in materials and workmanship for a period of **13 months** from date of purchase. OMEGA's WARRANTY adds an additional one (1) month grace period to the normal **one** (1) **year product warranty** to cover handling and shipping time. This ensures that OMEGA's customers receive maximum coverage on each product.

If the unit malfunctions, it must be returned to the factory for evaluation. OMEGA's Customer Service Department will issue an Authorized Return (AR) number immediately upon phone or written request. Upon examination by OMEGA, if the unit is found to be defective, it will be repaired or replaced at no charge. OMEGA's WARRANTY does not apply to defects resulting from any action of the purchaser, including but not limited to mishandling, improper interfacing, operation outside of design limits, improper repair, or unauthorized modification. This WARRANTY is VOID if the unit shows evidence of having been tampered with or shows evidence of having been damaged as a result of excessive corrosion; or current, heat, moisture or vibration; improper specification; misapplication; misuse or other operating conditions outside of OMEGA's control. Components in which wear is not warranted, include but are not limited to contact points, fuses, and triacs.

OMEGA is pleased to offer suggestions on the use of its various products. However, OMEGA neither assumes responsibility for any omissions or errors nor assumes liability for any damages that result from the use of its products in accordance with information provided by OMEGA, either verbal or written. OMEGA warrants only that the parts manufactured by the company will be as specified and free of defects. OMEGA MAKES NO OTHER WARRANTIES OR REPRESENTATIONS OF ANY KIND WHATSOEVER, EXPRESSED OR IMPLIED, EXCEPT THAT OF TITLE, AND ALL IMPLIED WARRANTIES INCLUDING ANY WARRANTY OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE ARE HEREBY DISCLAIMED. LIMITATION OF LIABILITY: The remedies of purchaser set forth herein are exclusive, and the total liability of OMEGA with respect to this order, whether based on contract, warranty, negligence, indemnification, strict liability or otherwise, shall not exceed the purchase price of the component upon which liability is based. In no event shall OMEGA be liable for consequential, incidental or special damages.

CONDITIONS: Equipment sold by OMEGA is not intended to be used, nor shall it be used: (1) as a "Basic Component" under 10 CFR 21 (NRC), used in or with any nuclear installation or activity; or (2) in medical applications or used on humans. Should any Product(s) be used in or with any nuclear installation or activity, medical application, used on humans, or misused in any way, OMEGA assumes no responsibility as set forth in our basic WARRANTY/DISCLAIMER language, and, additionally, purchaser will indemnify OMEGA and hold OMEGA harmless from any liability or damage whatsoever arising out of the use of the Product(s) in such a manner.

RETURN REQUESTS/INQUIRIES

Direct all warranty and repair requests/inquiries to the OMEGA Customer Service Department. BEFORE RETURNING ANY PRODUCT(S) TO OMEGA, PURCHASER MUST OBTAIN AN AUTHORIZED RETURN (AR) NUMBER FROM OMEGA'S CUSTOMER SERVICE DEPARTMENT (IN ORDER TO AVOID PROCESSING DELAYS). The assigned AR number should then be marked on the outside of the return package and on any correspondence.

The purchaser is responsible for shipping charges, freight, insurance and proper packaging to prevent breakage in transit.

FOR **WARRANTY** RETURNS, please have the following information available BEFORE contacting OMEGA:

- 1. Purchase Order number under which the product was PURCHASED,
- 2. Model and serial number of the product under warranty, and
- 3. Repair instructions and/or specific problems relative to the product.

FOR **NON-WARRANTY** REPAIRS, consult OMEGA for current repair charges. Have the following information available BEFORE contacting OMEGA:

- Purchase Order number to cover the COST of the repair,
- 2. Model and serial number of the product, and
- 3. Repair instructions and/or specific problems relative to the product.

OMEGA's policy is to make running changes, not model changes, whenever an improvement is possible. This affords our customers the latest in technology and engineering.

OMEGA is a registered trademark of OMEGA ENGINEERING, INC.

© Copyright 2016 OMEGA ENGINEERING, INC. All rights reserved. This document may not be copied, photocopied, reproduced, translated, or reduced to any electronic medium or machine-readable form, in whole or in part, without the prior written consent of OMEGA ENGINEERING, INC.

Where Do I Find Everything I Need for Process Measurement and Control? OMEGA...Of Course!

Shop online at omega.com ^{sм}

TEMPERATURE

Thermocouple, RTD & Thermistor Probes, Connectors, Panels & Assemblies

✓ Wire: Thermocouple, RTD & Thermistor

☑ Calibrators & Ice Point References

☑ Recorders, Controllers & Process Monitors

Infrared Pyrometers

PRESSURE, STRAIN AND FORCE

Transducers & Strain Gages

Load Cells & Pressure Gages

☑ Displacement Transducers

☑ Instrumentation & Accessories

FLOW/LEVEL

☑ Rotameters, Gas Mass Flowmeters & Flow Computers

☑ Turbine/Paddlewheel Systems

☑ Totalizers & Batch Controllers

pH/CONDUCTIVITY

☑ Benchtop/Laboratory Meters

Controllers, Calibrators, Simulators & Pumps

☑ Industrial pH & Conductivity Equipment

DATA ACQUISITION

Data Logging Systems

Wireless Sensors, Transmitters, & Receivers

☑ Signal Conditioners

Data Acquisition Software

HEATERS

Heating Cable

☑ Cartridge & Strip Heaters

☑ Immersion & Band Heaters

Flexible Heaters

☑ Laboratory Heaters

ENVIRONMENTAL MONITORING AND CONTROL

☑ Metering & Control Instrumentation

☑ Refractometers

Pumps & Tubing

Air, Soil & Water Monitors

☑ Industrial Water & Wastewater Treatment

LT-14468r2.0 20170112 M-4172/0117