

omega.com[®]

Ω OMEGA[®]

PSW-681, PSW-685 Pressure Switch

INSTRUCTION
SHEET

M-4461/0407

Shop online at: omega.com e-mail: info@omega.com
For latest product manuals: omegamanual.info


Set Point Adjustment:

Loosen the lock ring.

Turn interface either up or down until pointer is at the desired pressure or vacuum on range label.

Retighten the lock ring.

Verify adjustment by applying pressure or vacuum.



Electrical Wiring:

Wires are supplied in 12" lengths as standard.

Wires are 20 AWG PVC insulated.

Color Code in Gage: Black = Common, Red = N.C., White = N.O.

Color Code in Vacuum: Black = Common, Red = N.O., White = N.C.