

PSDIN-41000 Series Operators Guide



Issue A - Jan 2012

These power supplies are intended for installation by suitably qualified personnel in enclosures that provide safety protection and as such are not user accessible. They are convection cooled and provision must be made for free air to flow round the unit. Additional cooling will improve the long term reliability. This is normally achieved by mounting on a large metal surface, or if this is not possible by fan cooling.

AC CONNECTION AND FUSING

The 41000 SERIES regulated power supplies have link selectable inputs of 115 V AC or 230 V AC ($\pm 10\%$). See Figures 1 and 2 overleaf.

See input selection table. Inputs must be fused with a slow-blow (T) HBC type fuse. Suitable fuse types to comply with safety approvals WICKMANN 19181, LITTELFUSE Series 215.

DISCONNECT DEVICES

For PERMANENTLY CONNECTED EQUIPMENT, a readily accessible disconnect device shall be incorporated external to the equipment.

For PLUGGABLE EQUIPMENT, the socket-outlet shall be installed near the equipment and shall be easily accessible.

OVERLOAD PROTECTION

All models are fitted with foldback current limiting. This feature is factory set at 120% of I_{max} to minimise the risk of erroneous tripping due to line spikes etc. It is not recommended to run the power supply at greater than I_{max} continuously.

PARALLEL CONNECTION

1. Units of the same type may be connected in parallel in order to achieve greater output currents. In simple parallel operation the unit with the highest output voltage will supply the load current up to its limit whereon the next highest will provide the additional current up to its limit etc. To operate safely in this way the current limit should be adjusted to the nominal max unit current to avoid a constant overload situation.

2. In some cases it is desirable to have each supply capable of delivering 100% of the load current (parallel redundant); in this case the units should be connected as shown in figure 3 overleaf.

TECHNICAL SPECIFICATION

Input Voltage
115 or 230 V AC ($\pm 10\%$) link selectable, 50 to 60 Hz

Ripple & Noise
<5 mV rms

Output Voltage Tolerance
 $\pm 5\%$ maximum

Load Regulation
 $\pm 0.2\%$ for 50% load change

Line Regulation
 $\pm 0.05\%$ for 10% line change

Isolation: Input to Output
3750 V AC minimum

Temperature rating
Standard range: 0°C to +50°C full-rated, derated linearly to 40% at 70°C

Safety
In accordance with EN60950

Overall Dimensions
(l x w x h) 119.2 x 45 x 73.2 mm

Weight
0.37 kg (41245; 0.53 kg)

Material
Polycarbonate (self extinguishing to UL 94V-0)

Environmental Rating
IP20

INPUT CONNECTION

DIAGRAM 230 V AC




Figure 1

INPUT CONNECTION

DIAGRAM 115 V AC




Figure 2




Figure 3

GENERAL SPECIFICATION

Model	Output Voltage Volts	Output Current mA	Input fuse 115 V	Input fuse 230 V
41052R	5	200	0.5A	0.25A
41055R	5	500	0.5A	0.25A
41121R	12	100	0.5A	0.25A
41122R	12	200	0.5A	0.25A
41124R	12	400	0.5A	0.25A
41151R	15	100	0.5A	0.25A
41153R	15	300	0.5A	0.25A
41241R	24	100	0.5A	0.25A
41242R	24	200	0.5A	0.25A
41245R	24	500	0.5A	0.25A