RDXL6SD-USB Modbus over serial line interface

Interface

Assigned on installation	
1	
57600	
8 data, No parity, 2 stop	
20 max	

Supported functions

Read register 0x03, 0x04

Address table

<u>Address</u>	Description	<u>Data type</u>	<u>Array size</u>
0x1000	Unfiltered temperature ¹	Int32	6
0x100C	Differential temperature ¹	Int32	6
0x1018	Cold junction temperature ¹	Int32	4
0x1020	Voltage (μV)	Int32	4
0x1028	Resistance (mΩ)	Int32	2
0x102C	Maximum temperature ¹	Int32	6
0x1038	Minimum temperature ¹	Int32	6
0x1044	Average temperature ¹	Int32	6
0x1050	Standard deviation ²	Int32	6
0x105C	Alarm 1 status	UInt16	6
	0 = Alarm 1 not triggered		
	1 = Alarm 1 triggered		
0x1062	Alarm 2 status	UInt16	6
	0 = Alarm 2 not triggered		
	1 = Alarm 2 triggered		
0x1068	Channel type	UInt16	6
	0 = Туре К		
	1 = Type J		
	2 = Type T		
	3 = Type N		
	4 = Type E		
	5 = Type R		
	6 = Type S		
	7 = PT100 2-wire		
	8 = PT200 2-wire		
	9 = PT500 2-wire		
	10 = PT1000 2-wire		
	11 = PT100 3-wire		
	12 = PT200 3-wire		
	13 = PT500 3-wire		
	14 = PT1000 3-wire		
0x106E	Units	UInt16	1
	0 = °C, 1 = °F		

¹ Least significant bit is 0.1, units specified by "Units" register

² Least significant bit is 0.001, units specified by "Units" register

For further information please refer to http://www.modbus.org/specs.php For FTDI drivers please visit http://www.ftdichip.com/FTDrivers.htm