


Output Loop Powered DIN Rail Multi-Channel Isolators



DRI-LPO Series



DRI-LPO-2MA shown smaller than actual size.

- ✓ Provides One or Two Isolated 4 to 20 mA Output Current Loops in Proportion to One or Two DC Inputs
- ✓ High Density DIN Rail Mounting
- ✓ Prevents Ground Loops
- ✓ Plug-in Terminals
- ✓ Standard Input Ranges
- ✓ Output Loop Powered from 12 to 35 Vdc

The DRI-LPO Series are DIN rail mount, DC input, single or dual channel, isolating two-wire transmitters. Each channel accepts a DC voltage or current input and provides an isolated 4 to 20 mA output. Each channel is fully isolated (1800 Vdc) from input-to-output and channel-to-channel.

All DRI-LPO Series modules feature plug-in screw terminals for easy installation and low Mean-Time-To-Repair (MTTR). Two or more modules can slide together and interlock for solid, high density mounting. This is accomplished by removing either the foot, or the adjacent unit's faceplate (for right-hand side or left-hand side mounting, respectively). The module to be attached will easily slide on to the side of the mounted unit.

DC input, two-wire transmitters are used to isolate and convert a DC voltage or current into a proportional 4 to 20 mA signal. Two-wire transmitters are primarily used in remote locations near the sensor since they reduce the probability of signal errors and save wiring costs by utilizing the two power wires to send the 4 to 20 mA signal. The current signal is usually monitored by a control system or displayed for an operator.

Typically, DC voltages or currents from various field instruments (e.g. level, flow, pressure and position sensors) are used to monitor and control a manufacturing process. Voltage signals can only run a short distance to a panel without errors caused by noise or lead resistance in the wires. These sensor (voltage) signal wires are usually terminated at the two-wire transmitter and converted into a 4 to 20 mA signal which is highly immune to noise and not affected by lead resistance, both of which can cause significant errors in voltage signals transmitted over long distances. The 1800 Vdc isolation capability of the DRI-LPO Series prevents ground loops from causing errors in DC voltage or current signals and can reduce susceptibility to radio frequency interference (RFI). Isolation also provides protection from high voltages and current spikes which can damage expensive supervisory control and data acquisition (SCADA) equipment, such as a PLC or DCS.

The DRI-LPO Series operates as a two-wire transmitter; each channel derives its power from a 12 to 35 Vdc source connected in series with the 4 to 20 mA output loop. Typically a 24 Vdc source is used for power, allowing 12 Vdc (600 Ω @ 20 mA) for other devices connected in series in the current loop. The outputs of the DRI-LPO Series are isolated from the inputs and protected from reverse polarity. Zero and span pots are provided for each channel to calibrate the output to the input source (±5%). Standard input ranges are calibrated to rated accuracy. One range per module; one or two channels per module.



Specifications

INPUT

DRI-LPO-MA: 1 channel, 4 to 20 mA input

DRI-LPO-2MA: 2 channels, 4 to 20 mA input

DRI-LPO-V: 1 channel, 0 to 10V input

OUTPUT

DRI-LPO-MA, DRI-LPO-V: 1 channel, 4 to 20 mA output

DRI-LPO-2MA: 2 channels, 4 to 20 mA output

Impedance: ≥ 100 k Ω (voltage input); ≤ 20 Ω (4 to 20 mA input)

Protection: Withstands up to 24 Vdc (current input), 120 Vac (voltage input) without damage

Supply Voltage Range: 12 to 35 Vdc, each channel

Output Accuracy: $\leq 0.1\%$ of full-scale input typical, $\leq 0.2\%$ max @ 23°C including linearity, repeatability and hysteresis

Adjustability: Front accessed 10 turn pot, $\pm 5\%$ of span for zero and span, typical

Stability: $\leq 0.025\%/^{\circ}\text{C}$ of full-scale maximum

ESD Susceptibility: Meets IEC 801-2 level 2 (4kV)

Isolation: 1800 Vdc or peak AC between input and output and channel-to-channel

Response Time: 100 msec typical (10 to 90%)

Temperature:


Operating: -40 to 80°C (-40 to 176°F)

Storage: -40 to 80°C (-40 to 176°F)

Humidity (Non-Condensing): 15 to 90% RH @ 45°C (113°F)

Wire Terminals: Socketed screw terminals for 12 to 22 AWG

Weight: 154 g (0.34 lb)



OMEGACARESM extended warranty program is available for models shown on this page. Ask your sales representative for full details when placing an order. OMEGACARESM covers parts, labor and equivalent loaners.

To Order

Model No.	Description
DRI-LPO-MA	Single channel output loop powered DIN rail isolator, 4 to 20 mA input, 4 to 20 mA output
DRI-LPO-2MA	2 channel output loop powered DIN rail isolator 4 to 20 mA inputs, 4 to 20 mA outputs
DRI-LPO-V	Single channel output loop powered DIN rail isolator 0 to 10V input, 4 to 20 mA output
RAIL-35-1	35 mm DIN rail, 1 m (3.3') length
RAIL-35-2	35 mm DIN rail, 2 m (6.6') length

Ordering Example: **DRI-LPO-2MA** 2 channel output loop powered DIN rail isolator, **RAIL-35-1** 35 mm DIN rail, 1 m (3.3') length and **OCW-1** OMEGACARE extends standard 1-year warranty to a total of 2 years.