



Non-Fraying Fiberglass Sleeving

Braided Sleeving for High Temperature and Abrasive Applications

FBGS Series Starts at **\$0.19** Per Foot For 500' Spools



For More Sleeving Options, Visit omega.com/sleeving



FBGS-Y-20-25, yellow 20 gage fiberglass sleeving, \$6.25.




FBGS-R-20-25, red 20 gage fiberglass sleeving, \$6.25.

Both models shown actual size.

- ✓ High Temperature Rating to 316°C (601°F) Continuous Duty and 616°C (1141°F) for Short Periods
- ✓ Good Resistance to Most Alkalies
- ✓ Fair Resistance to Acids
- ✓ Unaffected by Bleaches and Solvents
- ✓ Flame Resistance, Will Not Burn
- ✓ Available in Standard Spools Lengths and Custom Foot Lengths

FBGS Series non-fray fiberglass sleeving is a flexible, high temperature primary or secondary insulation made from closely braided, continuous filament fiberglass which has been heat-cleaned to remove impurities in the yarn. Acrylic resin binders are applied for color coding and to further retard fraying and to hold sleeving round for cutting. This fiberglass insulation is unaffected indefinitely through a temperature range from -60 to 316°C (-76 to 601°F) and withstand up to 616°C (1141°F) for shorter periods. Colors will be less vivid after exposure to 150°C (302°F).

FBGS Series fiberglass sleeving is used for thermal and mechanical protection in consumer, commercial and industrial applications where flexibility, abrasion resistance or insulation is required and particularly when temperature extremes prohibit the use of other materials.



AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)		
Model Number	Price	Length of Spool m (ft)†
FBGS-(*)-(**)-25	\$6.25	7.6 (25)
FBGS-(*)-(**)-50	11.25	15.2 (50)
FBGS-(*)-(**)-100	21.25	30.5 (100)
FBGS-(*)-(**)-200	40.00	61 (200)
FBGS-(*)-(**)-500	93.75	152.4 (500)

(*) Select color, "B" = Blue, "BK" = Black, "R" = Red, "N" = Natural, "Y" = Yellow or "P" = Purple.

(**) Select gage; 20, 24, 26, 28 or 30.

† For non-stock lengths, please contact sales.

Ordering Examples: FBGS-R-24-25, 7.6 m (25') spool of 24 gage, red fiberglass sleeving, \$6.25. FBGS-B-20-200, 61 m (200') spool of 20 gage, blue fiberglass sleeving, \$40.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters