

LIGHTWEIGHT OIL IMMERSION HEATER

With 2 Element Design—2 NPT Steel Screw Plug

MTO-2 Series
Starts at





- ✓ Rugged Steel Sheath for Use with Lightweight Oils
- ✓ 1.5 to 6 kW
- ✓ 120, 208, 240 or 480V; 1 Phase
- ✓ General Purpose¹ NEMA-1 Rated and UL Listed Enclosure or Moisture Resistant/² Explosion Enclosure²

Note: The immersion heater should be used with an approved temperature control device to assure safe operation. See Temperature Section for our selection of process controllers.

SPECIFICATIONS

Wattage: 1.5 to 6 kW
Power: 120, 208, 240 or 480V; 1 phase
Watt Density: 23 to 26 W/in²
Sheath: 1.2 cm (0.475") diameter
Screw Plug: 2 NPT steel
Enclosure: E1 general purpose¹, NEMA-1 rated, or type E2 moisture resistant/explosion resistant enclosure.²



CAUTION AND WARNING!
 Fire and electrical shock may result if products are used improperly or installed or used by non-qualified personnel. See inside back cover for additional warning.



MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)									
kW	W/in ²	No. Htg. Elem.	Dim. B cm (in)	E1 General Purpose Enclosure ¹		Wt. kg (lb)	E2 Explos. /Moist Res. Encl. ²		Wt. kg (lb)
				Model No.	Price		Model No.	Price	
1.5	24	2	30 (11¾)	MTO-215A/*	\$295	1 (3)	MTO-215E2/*	\$550	3 (6)
2	24	2	45 (17¾)	MTO-220A/*	335	2 (4)	MTO-220E2/*	575	3 (7)
2.5	26	2	9 (19⅞)	MTO-225A/*	365	2 (4)	MTO-225E2/*	625	3 (7)
3	23	2	63 (24⅞)	MTO-230A/*	425	2 (4)	MTO-230E2/*	675	3 (7)
4	23	2	83 (32¾)	MTO-240A/*	500	3 (6)	MTO-240E2/*	750	4 (8)
5	23	2	102 (40¼)	MTO-250A/*	600	3 (7)	MTO-250E2/*	850	4 (8)

/*Designate voltage, i.e., insert "120" for 120 Vac, "208" for 208 Vac, "240" for 240 Vac, or "480" for 480 Vac.
 // * Designate voltage, ie., insert "208" for 208 Vac, "240" for 240 Vac, or "480" for 480 Vac.
¹ Heaters with General Purpose Enclosures are UL recognized and CSA Certified.
² Heaters with Moisture Resistant/Explosion Resistant Enclosures are CSA NRTL/C Certified.

Ordering Example: MTO-215A/240, 1.5 kW heater powered by 240 Vac, \$295.

Caution: Explosion resistant type E2 construction refers to heater design features which provide explosion resisting containment of electrical wiring according to National Electric Code. Abnormal application or use of heaters which in excessive temperatures can create hazardous conditions which can lead to fire



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters