HIGH TEMPERATURE HEATING TAPES

FGS, FGH, FWH Series

- ✓ Maximum Exposure Temperature up to 480°C (900°F)
- ✓ Reliable
- Fiberglass Insulated
- ✓ Fast Thermal Response
- ✓ Integral Molded Separable Plug
- Available with Leads Same End[†]

APPLICATIONS

Wide and heavy-duty insulated tapes are good for direct contact on a conductive surface.

Standard tapes are made from fine gage stranded resistance wires that are double insulated with braided fiberglass and knitted into flat tapes for maximum flexibility. A heavy insulated tape is made by taking a standard tape and braiding it between layers of fiberglass yarn. Wide tapes are made from two or more standard tapes that are sewn between two layers of fiberglass cloth.

SPECIFICATIONS

Heating Elements: 36-40 gage resistance wire.

Lead Wires: Emerge from opposite ends into separate sides

of an integrally molded separable plug

Heating Element Insulation: Double-braided fiberglass

Dielectric Strength: In excess of 2000 V

† To order heaters with power leads exiting the same end of the tape, add suffix "-LSE" to model number. To order 240 V version change the "1" in the part no. prior to the "-" to "2" for 240 V. All 240 V versions are not supplied with plugs. Consult Sales for prices.


CAUTION AND WARNING!


Fire and electrical shock may result if products are used improperly or installed or used by non-qualified personnel. See inside back cover for additional warnings.

Wide Heavy Insulated Tapes

To Order						
Watts	W/in²	Volts	Size	Model No.		
209	4.9	120	1¾" x 2'	FWH171-020		
418	4.9	120	1¾" x 4'	FWH171-040		
622	4.9	120	1¾" x 6'	FWH171-060		
836	4.9	120	1¾ x 8′	FWH171-080		
1045	4.9	120	1¾" x 10'	FWH171-100		
313	5.2	120	2½" x 2'	FWH251-020		
627	5.2	120	2½" x 4'	FWH251-040		
940	5.2	120	2½" x 6'	FWH251-060		
1254	5.2	120	2½" x 8'	FWH251-080		
1567	5.2	120	2½" x 10'	FWH251-100		
418	5.3	120	31/4" x 2'	FWH321-020		
836	5.3	120	31/4" x 4'	FWH321-040		
1254	5.3	120	31/4" x 6'	FWH321-060		
1672	5.3	120	31/4" x 8'	FWH321-080*		
2090	5.3	120	31/4" x 10'	FWH321-100*		

* Does not come with plug. Comes complete with instruction sheet.





Standard Insulated Tapes

To Order						
Watts	W/in ₂	Volts	Size	Model No.		
46	8.6	120	%" x 12"	FGS0031-010		
105	8.6	120	½" x 2'	FGS051A-020		
210	8.6	120	½" x 4'	FGS051A-040		
310	8.6	120	½" x 6'	FGS051A-060		
420	8.6	120	½" x 8'	FGS051A-080		
520	8.6	120	½" x 10'	FGS051A-100		
210	8.6	120	1" x 2'	FGS101-020		
420	8.6	120	1" x 4'	FGS101-040		
627	8.6	120	1" x 6'	FGS101-060		
830	8.6	120	1" x 8'	FGS101-080		
1045	8.6	240	1" x 10'	FGS102-100*		

Heavy Insulated Tapes

To Order							
Watts	W/in²	Volts	Size	Model No.			
105	8.6	120	½" x 2'	FGH051-020			
210	8.6	120	½" x 4'	FGH051-040			
310	8.6	120	½" x 6'	FGH051-060			
420	8.6	120	½" x 8'	FGH051-080			
520	8.6	120	½" x 10'	FGH051-100			
210	8.6	120	1" x 2'	FGH101-020			
420	8.6	120	1" x 4'	FGH101-040			
620	8.6	120	1" x 6'	FGH101-060			
830	8.6	120	1" x 8'	FGH101-080			
1045	8.6	120	1" x 10'	FGH101-100			