LEVEL SWITCH SYSTEMS



For Liquids Only



LVC Series



- ✓ No Moving Parts for Long Life
- ✓ Wide Chemical Compatibility
- ✓ Works for **Conductive Liquids**

The LVC500 Series electronic level controls should be used whenever a liquid level needs to be maintained, such as pumping down an industrial sump, or indicated, such as a holding tank high-level alarm. A system consists of 3 components: (1) cut-to-length threaded electrode rods; (2) single or multi-electrode holder; (3) remote electronic module(s).

The LVC500 Series operates on a simple conductance principle whereby a small electrical current is passed through the conductive liquid between 2 electrodes or an electrode and a metallic tank wall. For applications that require a separate start and stop point,

a single control module, plus LVC-E11 electrode 2 electrodes and a tank reference, is required. When several applications or levels are necessary within a single tank, an LVC-N3-SS, SS threaded electrode is needed for multi-electrode assembly each level (plus tank shown smaller than reference), plus a multi-electrode holder actual size. and a control module for each differential or single-level application. Typically, potable water, condensate, acids, and waterbased chemicals (inorganic chemicals) have sufficient conductivity. Non-aqueous liquids, such as oils and other hydrocarbons, cannot be measured.

Note:

Always treat hazardous areas with respect! If the electrodes or float switch is located in a hazardous area, an intrinsically safe control module must be used. Intrinsically safe controls must be installed by experienced personnel familiar with intrinsic safety wiring, and installation must be in accordance with the National Electrical Code (NEC). The control must be mounted in a non-hazardous location with the wiring to the level probes or float switch going into the hazardous atmosphere. Intrinsically safe wiring must be separated from non-intrinsically safe wiring, and the length of your 14 or 16 gage copper wire must not exceed the specifications listed in the current installation manual. Consult your local electrical code inspector for further details.

Electronics Modules Mounting Assemblies

- ✓ SPDT Relay Output
- ✓ Fully Field Selectable
- Transparent Case for Viewing Relay Status
- Low-voltage probe circuit
- SPDT relay output
- Interface to pumps, valves, or alarm systems
- Field-selectable latching/ non-latching operation
- Field-selectable high/low alarm, pump-up/pump-down

LVC510 Series:

- See-through Lexan® case for viewing relay status LED
- Plug-in module, socket included
- Screw terminal connections for easy wiring

LVC512 Model:

- Field-settable sensitivity to match a variety of liquids
- Required for distilled water (1 MΩ max)

LVC521 Model:

- · Open circuit board construction
- Low cost, OEM style
- Spade terminal connections
- Designed to mount on ¼₆" backplate with supplied plastic standoffs
- Relay status LED


LVC550 Series:

- Intrinsically safe
- Approved for Class I and II, Division 1, Groups A through G
- 8 A relay output
- LVC551: FM approved LVC552: UL approved
- Can be used with any non-powered switch closure

Electronics Operation Direct Mode Single-Level Service:

Single-Level Service:

For high or low alarms or cutoffs. When the liquid rises to the electrode on terminal H, the control energizes, changing the state of the load contacts. The control remains energized until the liquid level recedes below electrode on terminal H. The control then de-energizes, returning load contacts to original state.



Differential Service:

For fill or drain applications. When the liquid rises to the electrode on terminal H, the control energizes, changing the state of the load contacts. The control remains energized until the liquid level recedes below electrode on terminal L. The control then deenergizes, returning load contacts to original state.

Inverse Mode:

Control energizes with power, changing the state of the load contacts. All other responses are the opposite of the response given by direct-mode operation. Inverse mode is normally used for pump-up or high-level alarm applications.

SPECIFICATIONS

Supply Voltage: 102 to 132 Vac (110 to 132 Vac for LVC552), 50/60 Hz standard; 240 and 24 Vac optional)

Ambient Temperature: -40 to 65°C (-40 to 150°F)

Switch-Point Hysteresis:

1.6 mm (±1/16")

Relay Time Delay: ½ second delay on rising level

See chart below for additional information.

LVC-E11 electrode

MOUNTING ASSEMBLIES

Single Electrode:

The LVC-S Series comprises single electrode holders with exposed connection. UL-approved rubber boots are available for connection protection.

Shipping Weight:

LVC-S unit, 170 g (6 oz)

Overall Length: 82.6 mm (3.25") Multiple Electrodes:

The LVC-N and LVC-F mounting assemblies feature a gasketed, epoxy-coated, die-cast aluminum junction box, and include the proper number of electrode holders. See chart below for additional information.

Electrodes

The LVC-E electrodes come standard in 316 SS, but are available in a wide range of materials. Electrodes thread into couplings on LVC-S, LVC-N, and LVC-F mounting assemblies.

Electrode Diameter: 6.35 mm (1/4");

1/4" thread length
Electrode Weight:


0.25 g/mm (0.167 lb/ft)

Electronic Modules

LVC	Power	Dimensions: mm (inch)			Shipping Weight
Model	Consumption	Н	W	L	g (oz)
511	4.5 W	88.9 (3.5)	50.8 (2)	58.7 (2.31)	487 (20)
512	4.5 W	88.9 (3.5)	63.5 (2.5)	66.7 (2.62)	487 (20)
521	4.5 W	34.9 (1.37)	63.5 (2.5)	55.6 (2.19)	487 (20)
551	4.0 W	54 (2.12)	85.7 (3.37)	111.2 (4.18)	765 (27)
552	1.7 W	54 (2.12)	85.7 (3.37)	111.2 (4.18)	765 (27)

Multiple Electrode Assemblies

	No. of	Housing Dimensions: mm (inch)		Housing	
LVC Model	Electrodes	Н	W	L	Conduit Size
NX-BR/FX-BR	1	57.2 (2.25)	57.2 (2.25)	57.2 (2.25)	½ NPT
NX-BR/FX-BR	2 to 4	82.6 (3.25)	82.6 (3.25)	60.4 (2.37)	½ NPT
NX-BR/FX-BR	5 to 7	101.6 (4.0)	101.6 (4.0)	63.5 (2.5)	¾ NPT



Select electrode length as measured from the top of the tank to the required activation point. Determine the number of electrodes necessary for your application.

2

- Select mounting style to match tank. Select fitting that matches the number of electrodes selected. Select material to match liquid.
- Select the proper electronic module.



Ordering Example

It is desired to have a pump up control system in a plastic tank holding ordinary water. The components ordered are:

- 1) 1 LVC-E11 electrode
- 2) 2 LVC-E12 electrodes
- 3) 1 LVC511 electronics module
- 4) 1 LVC-N3-BR 2 MNPT brass, 3-electrode mounting assembly
- 5) One 100' roll of TX4-100 4-conductor shielded copper cable

The LVC-E electrodes are all threaded into the LVC-N3-BR. Low level is at 24" below the top (between the 2 LVC-E12 electrodes); high level is at 12" below the top (between the LVC-E12 and LVC-E11 electrodes). The LVC511A can be wired for pumpup control, as well as for pump-down, high-level, or low-level alarm. Three of the 4 conductors of the TX4-100 cable are connected to the 3 probe terminals inside the LVC-N3-BR mounting assembly.

Electrodes

To Order Model No. Model No. **Material Material** Length mm (inch) LVC-E11 303 SS LVC-E51 316 SS 305 (12) LVC-E12 303 SS LVC-E52 316 SS 610 (24) LVC-E13 303 SS LVC-E53 316 SS 915 (36) LVC-E14 LVC-E54 316 SS 303 SS 1220 (48) LVC-E15 303 SS LVC-E55 316 SS 1525 (60) LVC-E16 303 SS LVC-E56 316 SS 1830 (72)

Beyond 1.8 m (72"), probes require PTFE sleeving at the tip to prevent swaying probes from coming into contact with each other. For very long probes or in highly agitated tanks, spacers may also be required. Consult OMEGA® Flow Department for further details.

Threaded Single Electrode Holders

2	Model No.	Description	Wetted Materials	Maximum Pressure at Maximum Temperature	
	LVC-S3	% MNPT for 1 LVC-E electrode open terminal	316 SS/ PTFE	400 psig at 231°C (448°F)	

Threaded Multi-Electrode Assemblies (Includes Junction Box)

١	Stainless Steel	Brass	Cast Iron	Wt. kg (lb)	Description
/	LVC-N1-SS	LVC-N1-BR	LVC-N1-C	1.8 (3.9)	1 MNPT, for 1 LVC-E electrode
	LVC-N2-SS	LVC-N2-BR	LVC-N2-C	2.6 (5.7)	2 MNPT, for 2 LVC-E electrodes
	LVC-N3-SS	LVC-N3-BR	LVC-N3-C	3.25 (7.2)	2 MNPT, for 3 LVC-E electrodes
	LVC-N4-SS	LVC-N4-BR	LVC-N4-C	3.8 (8.4)	2½ MNPT, for 4 LVC-E electrodes
	LVC-N5-SS	LVC-N5-BR	LVC-N5-C	5.2 (11.4)	3 MNPT, for 5 LVC-E electrodes
	LVC-N6-SS	LVC-N6-BR	LVC-N6-C	5.2 (11.4)	3 MNPT, for 6 LVC-E electrodes
	LVC-N7-SS	LVC-N7-BR	LVC-N7-C	5.25 (11.6)	3 MNPT, for 7 LVC-E electrodes

All threaded assemblies rated for 250 psig, 208°C (406°F).

Flanged Multi-Electrode Assemblies (Includes Junction Box)

	Stainless Steel	Cast Iron	Nominal Pipe, Flange Size and Description	Flange Diagram mm (inch)	Weight kg (lb)
	LVC-F1-SS	LVC-F1-CI	1", for 1 LVC-E electrode	108 (4.25)	1.25 (2.75)
)	LVC-F2-SS	LVC-F2-CI	2", for 2 LVC-E electrodes	152 (6)	2.9 (6.5)
	LVC-F3-SS	LVC-F3-CI	2", for 3 LVC-E electrodes	152 (6)	3.0 (6.7)
	LVC-F4-SS	LVC-F4-CI	21/2", for 4 LVC-E electrodes	178 (7)	3.6 (7.9)
	LVC-F5-SS	LVC-F5-CI	3", for 5 LVC-E electrodes	190 (7.5)	5 (11)
	LVC-F6-SS	LVC-F6-CI	3", for 6 LVC-E electrodes	190 (7.5)	4.9 (10.9)
	LVC-F7-SS	LVC-F7-CI	3", for 7 LVC-E electrodes	190 (7.5)	4.9 (10.9)

Standard flange is 125# cast iron rated for 125 psig. 178°C (353°F): 150# 316 SS flange rated for 225 psig.

Standard Relay Electronics

	Model Number	Description	Maximum Media Resistance
3	LVC511	10 A resistive at up to 120 Vac, 8-pin socket	50,000
	LVC512	(Field adjustable from 4700 to 1 million Ω)	
	LVC521	10 A resistive at up to 120 Vac, open circuit board	50,000
	Intrinsical	y Safe Relay Electronics	
	LVC551 8 A resistive at up to 120 Vac, FM listed		(Field adjustable from 0 to 470,000 Ω)
	LVC552	8 A resistive at up to 120 Vac, UL listed	100,000

Comes complete with operator's manual.

Direct action standard; for inverse action, add suffix "-INV" to model number; LVC551 and LVC552, no additional cost.

Inverse normally used for pump-up or low-level applications. For 240 Vac operation, add suffix "-240VAC" to model number, for additional cost for the LVC552 and LVC512. For 24 Vdc operation, add suffix "-24V" to model number, for additional cost.