



# Rugged Handheld Environmental Meters With Rubber Bumper and Cover for Field Engineering

## Temperature Measurement

Dual Input Type K Thermocouple Thermometer  
**HHC201**

- ✓ 0.1% Accuracy
- ✓ Fast Temperature Response
- ✓ Display T1, T2 or T1-D2 Differential
- ✓ Functions: Hold/Min/Max/Max-Min/AVG/REL
- ✓ Auto Power-Off (10 Minutes)
- ✓ Backlight with Auto-Off (15 Seconds)

### Specifications

**Units:** °C or °F  
**Range:** -200 to 1372°C (-328 to 2500°F)  
**Resolution:**  
 0.1°: -100 to 1372°C (-148 to 2500°F) 1°: -200 to -100°C (-328 to -148°F)  
**Accuracy:** Type K thermocouple ITS-90  
 ±(0.1% rdg +1°C): -60 to 1372°C (-76 to 2500°F)  
 ±(0.1% rdg +2°C): -200 to -60°C (-328 to -76°F)  
**Operating Temperature:** 0 to 50°C (32 to 122°F)  
**Power:** 2 "AAA" batteries (included)  
**Battery Life:** 250 hours typical with alkaline batteries  
**Dimensions:** 24.7 x 50.9 x 132.9 mm (0.98 x 2.0 x 5.2")  
**Weight:** 148 g (5.2 oz)  
*Comes complete with batteries, carrying strap, protection cap, and thermocouple.*



HHC201 shown smaller than actual size.

Infrared Thermometer  
**HHC210**

- ✓ Laser Sighting
- ✓ Field of View 6:1
- ✓ Adjustable Emissivity 0.1 to 1.00
- ✓ Display IR Temperature, Ambient Temperature and IR-Ambient Differential Temperature
- ✓ Functions: Hold/Min/Max/Max-Min/AVG
- ✓ Auto Power-Off (10 Minutes)
- ✓ Backlight with Auto-Off (15 Seconds)

### Specifications

**Units:** °C or °F  
**Infrared Temperature:**  
**FOV:** 100 mm (4") @ 600 mm (24")  
**Range:** -30 to 550°C (-22 to 1022°F)  
**Resolution:** 0.1°  
**Accuracy:**  
 ±2°C: -30 to 100°C (-22 to 212°F)  
 ±2% rdg: 101 to 550°C (214 to 1022°F)  
**Air Temperature:**  
**Range:** -20 to 60°C (-4 to 140°F)



**Accuracy:**  
 ±0.5°C: 0 to 45°C (32 to 116°F)  
 ±1°C: -20 to 0°C (-4 to 32°F);  
 45 to 60°C (116 to 140°F)  
**Operating Temperature:** 0 to 50°C (32 to 122°F)  
**Power:** 2 "AAA" batteries (included)  
**Battery Life:** 40 hour with laser typical with alkaline batteries  
**Dimensions:** 24.7 x 50.9 x 132.9 mm (0.98 x 2.0 x 5.2")  
**Weight:** 148 g (5.2 oz)

*Comes complete with batteries, carrying strap, and protection cap.*

HHC210 shown smaller than actual size.





# Pressure Measurement



HHC280 shown smaller than actual size.



HHC281 shown smaller than actual size.

## Differential Manometer

### HHC280

- ✓ 0 to 40 inH<sub>2</sub>O/0 to 100 hPa
- ✓ HVAC System Troubleshooting
- ✓ Gas Pressure Measurements
- ✓ Compliant for Pitot Tubes for Measuring Air Velocity
- ✓ Dual Inputs P1 and P2
- ✓ Functions: Hold/Min/Max/Max-Min/AVG
- ✓ Auto Power-Off (10 Minutes)
- ✓ Backlight with Auto-Off (15 Seconds)

## Specifications

**Eight Selectable Units:** mmH<sub>2</sub>O, mmHg, psi, inH<sub>2</sub>O, inHg, hPa, mbar, Pa, plus m/s and fmp (for air velocity)

**Range:** 0 to 100 hPa/0 to 1019.7 mmH<sub>2</sub>O

**Resolution:** 0.1 hPa/0.1 mmH<sub>2</sub>O

**Accuracy:** ±0.03 hPa (0 to 0.30 hPa)  
 ±0.05 hPa (0.31 to 1.00 hPa)  
 ±0.1 hPa + 1.5% or rdg (rest of range)  
 ±0.3 mmH<sub>2</sub>O (0 to 3.0 mmH<sub>2</sub>O)  
 ±0.5 mmH<sub>2</sub>O (3.1 to 10.2 mmH<sub>2</sub>O)  
 ±1.02 mmH<sub>2</sub>O + 1.5% of rdg (rest of range)

**Operating Temperature:** 0 to 50°C (32 to 122°F)

**Power:** 2 "AAA" batteries (included)

**Battery Life:** 85 hours typical with alkaline batteries

**Dimensions:** 24.7 x 50.9 x 132.9 mm (0.98 x 2.0 x 5.2")

**Weight:** 113 g (4.0 oz)

*Comes complete with batteries, carrying strap, and protection cap.*

## Absolute Pressure Meter

### HHC281

- ✓ High Accuracy Absolute Pressure Measurement
- ✓ Barometric and Altitude Measurement
- ✓ Calculation of Barometric Pressure
- ✓ Functions: Hold/Min/Max/Max-Min/AVG
- ✓ Auto Power-Off (10 Minutes)
- ✓ Backlight with Auto-Off (15 Seconds)

## Specifications

**Eight Selectable Units:** hPa, mbar, Pa, mmH<sub>2</sub>O, mmHg, inH<sub>2</sub>O, inHg, psi, plus m and ft (for altitude)

**Range:** 300 to 1200 hPa

**Resolution:** 0.1 hPa

**Accuracy:** ±3 hPa

**Operating Temperature:** 0 to 50°C (32 to 122°F)

**Power:** 2 "AAA" batteries (included)

**Battery Life:** 600 hours typical with alkaline batteries

**Dimensions:** 24.7 x 50.9 x 132.9 mm (0.98 x 2.0 x 5.2")

**Weight:** 120 g (4.2 oz)

*Comes complete with batteries, carrying strap, and protection cap.*

Unit	Range	Resolution
mmH <sub>2</sub> O	0 to 1019.7	0.1
mmHg	0 to 75.00	0.01
psi	0 to 1.450	0.001
inH <sub>2</sub> O	0 to 40.14	0.01
inHg	0 to 2953	0.001
hPa	0 to 100.00	0.01
mbar	0 to 100.00	0.01
Pa	0 to 10000	1
FPM	*	1
m/s	*	0.1



# RPM/Light Measurement

## Light Meter

### HHC230



- ✔ Measures Light Intensity
- ✔ Wide Measuring Range 0 to 200,000 lux
- ✔ Spectral Response  $f < 8\%$
- ✔ Based on CIE Standard Illuminant A (2856K)
- ✔ Functions: Hold/Min/Max/Max-Min/AVG
- ✔ Auto Power Off (10 Minutes)
- ✔ Backlight with Auto-Off (15 Seconds)

## Specifications

**Range:** 0 to 200,000 lux; 0 to 18,580 fc  
**Accuracy:**  $\pm 3\%$  rdg + 10 digits (based on a light source 2856K)  
**Resolution:** 1 lux (0 to 19999), 10 lux (20,000 to 200,000), 1 fc (0 to 18,580)  
**Units:** lux/fc

**Operating Temperature:** 0 to 50°C (32 to 122°F)

### Typical Light Intensity Ranges (lux):

- Design/General Office:** 1500 to 2000
- Meeting Room:** 300 to 750
- Precision Assembly:** 1500 to 3000
- R&D Department:** 750 to 1500
- Packing/Measurement/Hallway:** 300 to 750

**Power:** 2 "AAA" batteries (included)  
**Battery Life:** 180 hours typical with alkaline batteries  
**Dimensions:** 24.7 x 50.9 x 132.9 mm (0.98 x 2.0 x 5.2")  
**Weight:** 116 g (4.0 oz)  
*Comes complete with batteries, carrying strap, and protection cap.*



HHC230 shown smaller than actual size.

## RPM Meter

### HHC250

- ✔ Non-Contact Optical RPM Measurement
- ✔ Wide Measuring Range up to 99999 rpm with LED Spot Marking and Reflective Tape on Object
- ✔ Measuring Range Up to 40 cm (15.7") (Depending on Ambient Light)
- ✔ Functions: Hold/Min/Max/Max-Min/AVG
- ✔ Auto Power-Off (10 Minutes)
- ✔ Backlight with Auto-Off (15 Seconds)



## Specifications

**Range:** 100.0 to 99999  
**Accuracy:**  $\pm 0.02\%$  of rdg + 1 digit  
**Resolution:**  
 0.1 rpm: 100.1 to 19999.9 rpm  
 0.1 rps: 1.7 to 333.3 rps  
 1 rpm: 20,000 to 99,999  
 1 rps: 334 to 1666 rps

**Units:** rpm/rps  
**Operating Temperature:** 0 to 50°C (32 to 122°F)  
**Power:** 2 "AAA" batteries (included)  
**Battery Life:** 30 hours typical with alkaline batteries  
**Dimensions:** 24.7 x 50.9 x 132.9 mm (0.98 x 2.0 x 5.2")  
**Weight:** 110 g (3.9 oz)

*Comes complete with batteries, carrying strap, protection cap, and reflective tape (5 each).*



HHC250 shown smaller than actual size.



# Air Flow/Humidity/Dew Point/Wet Bulb



## Hygro-Anemometer

### HHC261

- ✔ 0.4 to 20 m/s (80 to 4000 ft/min)
- ✔ High Accuracy Air Flow Measurement
- ✔ Built-In Ambient Temperature Measurement
- ✔ Wind Chill Temperature (WCT) Indicator
- ✔ Integrated Flow Vane
- ✔ Humidity with Dew Point and Wet Bulb
- ✔ Functions: Hold/Min/Max/Max-Min/AVG
- ✔ Auto Power-Off (10 Minutes)
- ✔ Backlight with Auto-Off (15 Seconds)



HHC261 shown smaller than actual size.

## Specifications

### Air Velocity:

- Range: 0.4 to 20 m/s (80 to 4000 ft/min)
- Accuracy:  $\pm 0.2$  m/s + 2% of rdg;  $\pm 0.40$  ft/min + 2% of rdg
- Resolution: 0.1 m/s, 1 ft/min
- Units: beau, m/s, ft/m, mph, km/h, WCT, kts

### Air Temperature:

- Range: -20 to 60°C (-4 to 140°F)
- Accuracy:
  - $\pm 0.5^\circ\text{C}$ : 0 to 45°C (32 to 113°F)
  - $\pm 1^\circ\text{C}$ : -20 to 0°C and 45 to 60°C (-4 to 32°F) and (113 to 140°F)
- Resolution: 0.1°C/°F

### Humidity:

- Range: 0 to 100% RH
- Accuracy:
  - $\pm 2.5\%$ : 10 to 90% RH
  - $\pm 5\%$ : 0 to 10% RH and 90 to 100% RH

Operating Temperature: 0 to 50°C (32 to 122°F)

Power: 2 "AAA" batteries (included)

Battery Life: 50 hours typical with alkaline batteries

Dimensions: 24.7 x 50.9 x 132.9 mm (0.98 x 2.0 x 5.2")

Weight: 119 g (4.2 oz)

Comes complete with batteries, carrying strap, and protection cap.

**All Models Include Slip-Off Hard Cover Shell**

HHC201 shown closed with included cover.



HHC201 shown with included cover.

