

DIFFUSED SEMICONDUCTOR PRESSURE TRANSDUCER

STANDARD AND METRIC MODELS

0-5 Vdc Output

0-15 to 0-300 psi-Standard Models

0-1 to 0-16 bar-Metric Models

1 bar = 14.5 psi

1 kg/cm² = 14.22 psi

1 atmosphere = 14.7 psi = 29.93

inHg = 760.2 mmHg = 1.014 bar



PX6000C1-100G5T,
shown actual size.



VOLTAGE OUTPUT
PRESSURE TRANSDUCERS

B

PX6000/PXM6000 Series



Standard

- ✓ High Reliability
- ✓ Long-Term Stability
- ✓ All Stainless Steel Case
- ✓ Vacuum Range Available

OMEGA's PX6000/PXM6000 pressure transducers fit easily into your applications. This low-cost transducer is small and light, and mounting requires no bulky structures. You select from 3 electrical terminations and 6 pressure fittings. The sensor is a small [about 2.5 mm (0.1")] square silicon chip with 4 diffused strain gages, mounted in the stainless steel case. Laser-trimmed resistors provide temperature compensation and adjust zero balance and span.

The PX6000 Series uses solid state media isolation for improved reliability. Thin films of chemically inert materials are deposited or grown on the chip surface to provide electrical isolation between the sensor and the pressure medium. The sensor is less sensitive to vibration and more dependable in high-shock environments because the films add no significant mass. Corrosion resistance is outstanding, and the isolation will remain effective because there is no gel or oil column to deteriorate.

SPECIFICATIONS

Excitation: 16 to 38 Vdc unregulated

Output: 0 to 5 Vdc ± 0.1 Vdc
adjustable $\pm 10\%$ FSO

Input Current:

15 mA maximum with no load

Output Resistance: Less than 200 Ω

Zero Balance: 0V ± 0.1 Vdc

Adjustable $\pm 5\%$ FSO

Dielectric Isolation Resistance:

100 M Ω minimum at 45 Vdc applied
between the case or a conductive
medium and the bridge circuit

Sensing Element: 4-active-arm bridge
using a micro-machined diffused silicon
diaphragm sensor, thin-film media and
dielectric isolation barriers

Temperature Sensor: Output

resistance @ 24°C (75°F)

900 to 1500 Ω

Temperature Coefficient:

8% min, 10% maximum per 55.5°C
(100°F)

Accuracy: Combined linearity,
hysteresis and repeatability $\leq \pm 0.25\%$
FSO for all ranges

Operational Temp Range:

-54 to 121°C (-65 to 250°F)

Compensated Temp Range:

-18 to 82°C (0 to 180°F)

Thermal Effects:

Span: $\leq \pm 0.03\%$ FSO/°C (0.054%/°C)

Zero: $\leq \pm 0.03\%$ FSO/°C (0.054%/°C)

Vibration Sensitivity: At 20 g peak
sinusoidal vibration from 10 Hz to
2000 Hz ($\frac{1}{2}$ " D.A.), the output shall not
exceed 0.04% FSO/g for 15 psi range to
0.005% FSO/g for 100 psi and above

Natural Frequency: Greater than
35 kHz for 7 bar (100 psi) and above

Shock: 100 g, 11 ms half sine wave
without damage

Proof Pressure:

2 times rated pressure will not cause
changes in performance beyond the
specified tolerances

Burst Pressure: 3 times rated
pressure for pressure ranges below
14 bar (200 psi), or 2.5 times rated
pressure for pressure ranges above
200 psi will not cause rupture of the
pressure sensor

Wetted Parts: 316 stainless steel,
silicon, Pyrex® glass, epoxy, Kovar®

Electrical Connection: See Custom
Configurations, next page


Pressure Port: See Custom
Configurations, next page

Weight: 170 g (6 oz) typical

Mating Connector (Style 1):


PTS06A-10-6S-R (sold separately)

DIN	Pin	Wire Code
1	A	RED = + Input
3	B	GRN = + Output
	C	BLU = Common
2	D	WT = Common
	E	BLK = Temp. Sensor
	F	ORG = Temp. Sensor
		Shield = N/C



Dimensions: mm (inch)


DIFFUSED SEMICONDUCTOR TRANSDUCER



STANDARD CUSTOM CONFIGURATIONS

PX6000 SERIES	PRESSURE PORT [1]	ELECTRICAL CONNECTION [2]	RANGE (psi) [3]	UNITS [4]	OUTPUT [5]	CALIBRATION OPTION [6]
	A = 1/8-27 NPT male B = 1/8-27 NPT female C = 1/4-18 NPT male D = 1/4-18 NPT female L = MS33656-4 male M = MS33649-4 female		30* 015 020 050 100 200 300	VAC G,A G,A G,A G,A G,A G,A	5T = 0 to 5 Vdc output	CAL11 = 11-point NIST calibration additional cost [7] CABLE LENGTH -XXXFT ** available when selection [2] = 0 **
0 = 0.6 m (2') cable (std) additional cost/ft over 0.6 m (2') 1 = PTIH-10-6P connector (or equal, no charge). Mating connector (sold separately), order PTS06A-10-6S-R . 6 = mini DIN connector (no charge); (no temp sensor)			* Referenced to atmospheric pressure, 30 Vac range is 30 to 0 inHg vacuum, all other ranges are psi.			
			To order a custom configuration: 1. Select a pressure port 2. Select electrical connection 3. Select a pressure range 4. Select pressure units 5. Select output 6. Select options and agency approvals 7. Select extra length cable			

Ordering Examples: **PX6000M1-100G5T**, 100 psi vented gage pressure transducer with MS33649-4, female pressure connection, PTIH-10-6P, electrical connector and 0 to 5 V output. **PTS06A-10-6S-R**, mating connector (sold separately).
PX6000A0-30VAC5T-25FT, 30 to 0 inHg vacuum transducer with a 1/8-27 NPT male pressure connection, a reverse-acting (30 inHg vacuum = full scale output) 0 to 5 output, and 7.6 m (25') cable. **PX6000L1-015A5T**, 15 psi absolute pressure transducer with MS33656-4, male pressure connection, PTIH-10-6P, electrical connector and 0 to 5 Vdc output.
PTS06A-10-6S-R, mating connector (sold separately).



METRIC CUSTOM CONFIGURATIONS

PXM6000 CUSTOM CONFIGURATIONS						
PXM6000 SERIES	PRESSURE PORT [1]	ELECTRICAL CONNECTION [2]	RANGE (BAR) [3]	UNITS [4]	OUTPUT [5]	CALIBRATION OPTION [6]
MA = G½B Male additional cost			1.0	G,A	5T = 0 to 5 Vdc output	CAL11 = 11-point NIST calibration additional cost
MB = G½B Female no charge			1.6	G,A		
MC = G¼B Male additional cost			4.0	G,A		
MD = G¼B Female no charge			6.0	G,A		
			10	G,A		[7] CABLE LENGTH
			16	G,A		-XXXM
	0 = 0.6 m (2') cable (std) additional cost/m over 0.6 m (2')				** available when selection [2] = 0 **	
	1 = PTIH-10-6P connector (or equal, no charge)					
	6 = mini DIN connector (no charge) (no temp sensor)					
To order a custom configuration:						
1. Select a pressure port						
2. Select electrical connection						
3. Select a pressure range						
4. Select pressure units – absolute, gage						
5. Select output						
6. Select options and agency approvals						
7. Select extra length cable						
Visit us online for additional options including extended compensated temperatures.						

Ordering Examples: **PXM6000MB0-010BARG5T**, 10 bar gage pressure transducer with G 1/8B female connection and 0.6 m (2') cable termination, 0 to 5V output.
PXM6000MD1-010BARA5T, 10 bar absolute pressure transducer with G 1/4B female connection, 0 to 5V output, and twist-lock connector.
PTS06A-10-6S-R, mating connector (sold separately).



STANDARD
PX6000C6-200G5T,
shown smaller
than actual size.

STANDARD MODELS

To Order

MODELS WITH 0 TO 5 VDC OUTPUT, 1/4NPT-M PRESSURE CONNECTION

RANGE		MODEL NO.	COMPATIBLE METERS**
VACUUM			
30 to 0 inHg	102 to 0 kPa	PX6000C[*]1-30VAC5T	DP41-E, DP25B-E, DP24-E
ABSOLUTE PRESSURE			
0 to 15 psi	0 to 1.0 bar	PX6000C[*]-015A5T	DP41-E, DP25B-E, DP24-E
0 to 20 psi	0 to 1.4 bar	PX6000C[*]-020A5T	DP41-E, DP25B-E, DP24-E
0 to 50 psi	0 to 3.4 bar	PX6000C[*]-050A5T	DP41-E, DP25B-E, DP24-E
0 to 100 psi	0 to 6.9 bar	PX6000C[*]-100A5T	DP41-E, DP25B-E, DP24-E
0 to 200 psi	0 to 13.8 bar	PX6000C[*]-200A5T	DP41-E, DP25B-E, DP24-E
0 to 300 psi	0 to 20.7 bar	PX6000C[*]-300A5T	DP41-E, DP25B-E, DP24-E
GAGE PRESSURE			
0 to 15 psi	0 to 1.0 bar	PX6000C[*]-015G5T	DP41-E, DP25B-E, DP24-E
0 to 20 psi	0 to 1.4 bar	PX6000C[*]-020G5T	DP41-E, DP25B-E, DP24-E
0 to 50 psi	0 to 3.4 bar	PX6000C[*]-050G5T	DP41-E, DP25B-E, DP24-E
0 to 100 psi	0 to 6.9 bar	PX6000C[*]-100G5T	DP41-E, DP25B-E, DP24-E
0 to 200 psi	0 to 13.8 bar	PX6000C[*]-200G5T	DP41-E, DP25B-E, DP24-E
0 to 300 psi	0 to 20.7 bar	PX6000C[*]-300G5T	DP41-E, DP25B-E, DP24-E

Comes complete with 5-point NIST traceable calibration.

[*] Insert "0" for 0.6 m cable, "1" for twist-lock connector or "6" for mini DIN connector.

** Visit us online for compatible meters.

Ordering Examples: PX6000C1-050G5T, 50 psi gage pressure transducer with 0 to 5 Vdc output, PTIH-10-6P electrical connection and MS33656-4 male pressure port. PTS06A-10-6S-R, mating connector (sold separately).

PX6000C1-015A5T, 15 psi absolute pressure transducer with 0 to 5 Vdc output, PTIH-10-6P electrical connection and MS33656-4 male pressure port. PTS06A-10-6S-R, mating connector (sold separately).

ACCESSORY

MODEL NO.	DESCRIPTION
PTS06A-10-6S-R	Mating connector for PX6000 Series units with twist-lock connector

METRIC MODELS

MODELS WITH G1/4 MALE PRESSURE CONNECTION, CABLE OR CONNECTOR AND 0 TO 5 VDC OUTPUT

RANGE		MODEL NO.	COMPATIBLE METERS**
ABSOLUTE PRESSURE			
0 to 1 bar	0 to 15 psi	PXM6000MC[*]-001BARA5T	DP41-E, DP25B-E
0 to 1.60 bar	0 to 23 psi	PXM6000MC[*]-1.60BARA5T	DP41-E, DP25B-E
0 to 4 bar	0 to 58 psi	PXM6000MC[*]-004BARA5T	DP41-E, DP25B-E
0 to 6 bar	0 to 87 psi	PXM6000MC[*]-006BARA5T	DP41-E, DP25B-E
0 to 10 bar	0 to 145 psi	PXM6000MC[*]-010BARA5T	DP41-E, DP25B-E
0 to 16 bar	0 to 232 psi	PXM6000MC[*]-016BARA5T	DP41-E, DP25B-E
GAGE PRESSURE			
0 to 1 bar	0 to 15 psi	PXM6000MC[*]-001BARG5T	DP41-E, DP25B-E
0 to 1.60 bar	0 to 23 psi	PXM6000MC[*]-1.60BARG5T	DP41-E, DP25B-E
0 to 4 bar	0 to 58 psi	PXM6000MC[*]-004BARG5T	DP41-E, DP25B-E
0 to 6 bar	0 to 87 psi	PXM6000MC[*]-006BARG5T	DP41-E, DP25B-E
0 to 10 bar	0 to 145 psi	PXM6000MC[*]-010BARG5T	DP41-E, DP25B-E
0 to 16 bar	0 to 232 psi	PXM6000MC[*]-016BARG5T	DP41-E, DP25B-E
0 to 25 bar	0 to 363 psi	PXM6000MC[*]-025BARG5T	DP41-E, DP25B-E

Comes complete with 5-point NIST traceable calibration.

[*] Insert "0" for 0.6 m cable, "1" for twist-lock connector or "6" for mini DIN connector.

** Visit us online for compatible meters.

Ordering Examples: PXM6000MC0-010BARG5T, 10 bar gage pressure transducer with 0 to 5 Vdc output, 0.6 m (2') cable and G1/4 male pressure port.

PXM6000MC6-01.6BARA5T, 1.6 bar absolute pressure transducer with 0 to 5 Vdc output, mini DIN electrical connector and G1/4 male pressure port. Mating connector included.



VOLTAGE OUTPUT
PRESSURE TRANSDUCERS

B