

# SERIES 1950G | EXPLOSION-PROOF DIFFERENTIAL PRESSURE SWITCH



#### **BENEFITS/FEATURES**

- ATEX approved explosion proof for natural gas applications
- External set point screw provides easy access without opening or disassembling enclosure
- Easily accessible electrical connection simplifies the installation
- · Isolated process chambers from electrical compartment

#### **APPLICATIONS**

- · Natural gas applications
- · Process applications
- · All-weather applications


## **DESCRIPTION**


The Series 1950G Explosion-Proof Differential Pressure Switch combines the best features of the popular Dwyer® Series 1900 Pressure Switch with the benefit of natural gas compatibility. Units are rain-tight for outdoor installations, and are UL listed for use in class I, groups A, B, C, and D; class II, groups E, F, and G and class III atmospheres, directive 2014/34/EU (ATEX) compliant for **(€** 2813 **(x)** II 2G Ex db IIB+H<sub>2</sub> T6, CSA and FM approved for class I, div. 1, groups B, C, D; class II, div. 1, groups E, F, G and class III atmospheres, and IECEx Ex db IIB+H2 T6 (-40°C<Ta<+60°C). UKCA Ex compliant for ⟨€x⟩ II 2G Ex db IIB+H2 T6 Gb (C) Ex db IIB+H2 T6 Gb. The 1950G is very compact, about half the weight and bulk of equivalent conventional explosion-proof switches. Easy access to the SPDT relay and power supply terminals is provided by removing the top plate of the aluminum housing. A supply voltage of 24 VDC, 120 or 240 VAC is required. A captive screw allows the cover to swing aside while remaining attached to the unit. Adjustment to the set point of the switch can be made without disassembly of the housing.

### **SPECIFICATIONS**

Service	Air and compatible combustible gases.
Wetted Materials	Consult factory.
Temperature Limits	0 to 140°F (-17 to 60°C). Note: Set point drift may occur with ambient temperature changes.
Pressure Limits (Continuous)	45 in w.c. (11.2 kPa) continuous; 10 psig (68.95 kPa) surge.
Enclosure Rating	NEMA 3 (IP54), NEMA 7 and 9.
Switch Type	1 form C relay (SPDT).
Electrical Rating	10 A, 120/240 VAC, 28 VDC. Resistive 50 mA, 125 VDC.
Power Requirements	24 VDC ±10%. 120 or 240 VAC ±10% optional.
Electrical Connections	Internal terminal block.
Process Connections	1/8" female NPT.
Mounting Orientation	Diaphragm in vertical position. Consult factory for other position orientations.
Set Point Adjustment	Screw type on top of housing.
Weight	2 lb 15.7 oz (1.35 kg).
Compliance	ATEX, CCC, CE, CSA, FM, IECEx, KCs, PESO, UKCA Ex, UL.


#### WIRING DIAGRAM





## **HOW TO ORDER**

Use the **bold** characters from the chart below to construct a product code.



## **ORDER ONLINE TODAY!**

dwyer-inst.com/Product/Series1950G



**DWYER INSTRUMENTS, LLC** 

©Copyright 2022 Dwyer Instruments, LLC Printed in U.S.A. 8/22

DS-1950G Rev. 4