


# HANI™ Clamp Sensor - High Accuracy Non-Invasive Clamp Temperature Sensor for Sanitary Applications



Hybrid temperature sensing on metal pipes integrated with Layer N connectivity

- Non-invasive temperature measurement
- Measure the fluid temperature inside of a metal pipe
- Accuracy for Sanitary Metal Pipes:  $\pm 0.5^{\circ}\text{C}$  ( $\pm 0.9^{\circ}\text{F}$ )
- Response time<sup>1</sup> = 5 sec (t63) / 10 sec (t90)
- 4 to 20 mA loop powered analog output
- 0 to 100°C process temperature range
- Available for 1.5 to 4" pipe diameters (other sizes on request)
- Omega Smart Core enabled
  - Data logging
  - Plug and play device detection
- IP65 environmental rating
- Patent pending



## Ease of Installation

### Install your HANI™ Clamp Sensor in seconds

Omega's innovative clamp-on design makes sensor installation easy. Unlike invasive sensors, HANI™ Clamp Sensors mount to the outside of a metal pipe and read the temperature of the process media inside the pipe.

- No drilling
- No welding
- No downtime

Need to relocate the sensor?  
Un-clamp and go!

## Non-Invasive & Non-Contact Operation

### No penetration, no risk of contamination

The HANI™ Clamp Sensor never comes into contact with the process media flowing through the pipe. There is no risk of buildup, sensor wear or breakage from high flow rates, corrosive/abrasive liquids, wake frequency and water hammer.

## High Accuracy & Fast Response Times

### Performs like an invasive sensor

Omega's patent pending *Hybrid Temperature Sensing* platform uses

multiple sensors and a proprietary algorithm to achieve the same accuracy and fast response times as state-of-the-art invasive sensors without the cost and risk.

## Common Applications

### New and retrofitting existing systems


Lower the total cost of ownership and reduce contamination risk without sacrificing performance by upgrading to a HANI™ Clamp Sensor.

### Quality control & ad-hoc sensing

Clamp-on the sensor in seconds and connect to your laptop or PC for readings anytime - anywhere.

### Verify existing invasive sensors

With accuracies comparable to most state-of-the-art invasive sensors, the HANI™ Clamp Sensor can easily be placed next to an invasive sensor to verify the accuracy or determine the drift of the invasive sensor.



## Specifications

### Input Power

**Voltage:** 8 V<sub>DC</sub> - 28 V<sub>DC</sub>  
(loop powered)

### Max Loop Resistance:

$$R_{\max} (\Omega) = (V_{\text{supply}} - 8V) / 0.24 \text{ A}$$

### Analog Output

**Current:** 4 to 20 mA

### Process Parameters

**Process Medium:** Water, water-based fluids (others upon request)

**Pipe Materials:** Metal pipes

### Sanitary Pipe Diameters:

1.5", 2", 2.5", 3", 4" (others on request)

### Process Temperature Range:

0 to 100°C liquid, user scalable analog output

### Performance

#### Accuracy with fluid flowing:

±0.5°C

**Response Time (t63):** 5 seconds

**Response Time (t90):** 10 seconds

### Environmental

#### Ambient Operating Temperature:

0 to 40°C (32 to 104°F)

**Rating:** IP65 when mated

### Mechanical

#### Dimensions:

60.3 W x 64.31 L x 51.54 mm H

(2.38 W x 2.53 L x 2.03" H)



**Materials:** PA12, silicone rubber, nickel-plated brass, stainless steel

### General

**Agency Approvals:** CE, EMC, UKCA, 2014/30/EU, LVD 2014/35/EU class II product, (low voltage 8 to 28 V<sub>DC</sub>)

### Smart Core Enabled

Smart Core is integral to all Layer N integrated Smart Sensing devices. In addition to allowing for modular integration using any Layer N Smart Interface, this powerful suite of advanced features enables alarms and notifications, data assurance, data logging, storage, wireless connectivity and SYNC configuration.



Sensor Pipe Diameters	A	B	C
1.0, 1.5, 2.0	64.3 (2.53)	87.6 (3.45)	51.5 (2.03)
2.5, 3.0, 4.0	65.9 (2.60)	91.0 (3.58)	47.4 (1.87)

Sensor Dimensions: mm (in)

## Frequently Asked Questions

### How can a clamp-on temperature (surface) sensor have response times and accuracy similar to an immersion sensor?

Omega's innovative HANI™ Clamp Sensor includes multiple sensors along with a proprietary algorithm to reach response times and accuracy comparable to an immersion sensor.

### Will ambient temperature affect the reading of the HANI™ Clamp Sensor?

Ambient temperature will not affect the reading of the HANI™ Clamp Sensor. Operating temperature for the clamp-on sensor is 0 to 40°C (32 to 104°F).

### Is there any special preparation required to properly setup and mount the HANI™ Clamp Sensor?

There is no special preparation or tools required to setup and mount the sensor, however, when setting up any sensor ensure the mounting area is clean, dry, and free from any debris.

### How should the sensor be oriented on the pipe?

The sensor can be mounted on any straight pipe at least 2.5" long. It is suggested to mount the sensing surface on the bottom half of the pipe for best results.

### Are other pipe diameters / sizes available?


Yes, other diameters / sizes are available. Please contact us to discuss your specific application.

### Other than water-based process mediums, can other liquids and viscosities be measured?

Yes, please contact us to discuss your specific application.

## M12 8-Pin Wiring

Pin	Name	Function	Wiring
Pin 1	Loop -	4 to 20 mA Return	4 to 20 mA
Pin 2	INTR	Interrupt Signal	Layer N
Pin 3	SCL	I2C Clock Signal	Layer N
Pin 4	SDA	I2C Data Signal	Layer N
Pin 5	Shield	Shield Ground	Layer N
Pin 6	Loop +	4 to 20 mA Source	4 to 20 mA
Pin 7	GND	Power Ground	Layer N
Pin 8	3.3VDD	Power Supply	Layer N



## HANI™ Clamp Temperature Sensor for Sanitary Metal Pipes

Model Number	Process Temp Range	Pipe Size	Accuracy	Response Time	Features
HANI-C-1.5S-M-MA	0° (32°F) to 100°C (212°F)	1.5"	±0.5°C	5 sec (t63), 10 sec (t90)	—
HANI-C-1.5S-M-MA-CAL-3	0° (32°F) to 100°C (212°F)	1.5"	±0.5°C	5 sec (t63), 10 sec (t90)	Cal/Cert
HANI-C-2.0S-M-MA	0° (32°F) to 100°C (212°F)	2.0"	±0.5°C	5 sec (t63), 10 sec (t90)	—
HANI-C-2.0S-M-MA-CAL-3	0° (32°F) to 100°C (212°F)	2.0"	±0.5°C	5 sec (t63), 10 sec (t90)	Cal/Cert
HANI-C-2.5S-M-MA	0° (32°F) to 100°C (212°F)	2.5"	±0.5°C	5 sec (t63), 10 sec (t90)	—
HANI-C-2.5S-M-MA-CAL-3	0° (32°F) to 100°C (212°F)	2.5"	±0.5°C	5 sec (t63), 10 sec (t90)	Cal/Cert
HANI-C-3.0S-M-MA	0° (32°F) to 100°C (212°F)	3.0"	±0.5°C	5 sec (t63), 10 sec (t90)	—
HANI-C-3.0S-M-MA-CAL-3	0° (32°F) to 100°C (212°F)	3.0"	±0.5°C	5 sec (t63), 10 sec (t90)	Cal/Cert
HANI-C-4.0S-M-MA	0° (32°F) to 100°C (212°F)	4.0"	±0.5°C	5 sec (t63), 10 sec (t90)	—
HANI-C-4.0S-M-MA-CAL-3	0° (32°F) to 100°C (212°F)	4.0"	±0.5°C	5 sec (t63), 10 sec (t90)	Cal/Cert

CAL-3 option is a 3 point calibration at 10°, 50° and 90° C. CAL-4 option is a user selected number and value of temperature points, please contact us for a quote.

## Layer N Smart Interface

Layer N Smart Sensing devices require a Layer N Smart Interface to operate and connect to your Layer N Ecosystem. There are both wired and wireless options. Omega Sync software is free and enables you to read the fluid temperature digitally in just a few seconds.

Model Number	Description
IF-001	USB Smart Interface
IF-002	RS485/Modbus Smart Interface
IF-006-1-NA	Wireless Interface 915 MHZ (for North America)
IF-006-1-EU	Wireless Interface 868 MHZ (for Europe)

## Accessories

Model Number	Description
M12.8-T-SPLIT	Smart Probe M12-8 pin shielded T-splitter — enables access to I/O pins
M12.8-S-F-FM	M12-8 pin female straight plug field install connector with screw terminals
DM12CAB-8-1-RA	1m (3.3') cable dual M12-8 connector, right angle terminator
DM12CAB-8-3-RA	3m (9.8') cable dual M12-8 connector, right angle terminator
DM12CAB-8-5-RA	5m (16.4') cable dual M12-8 connector, right angle terminator
DM12CAB-8-1	1m (3.3') cable dual M12-8 straight connector
DM12CAB-8-3	3m (9.8') cable dual M12-8 straight connector
DM12CAB-8-5	5m (16.4') cable dual M12-8 straight connector