


OMB-DBK15

Universal Current/Voltage Input Card for OMB-LOGBOOK and OMB-DAQBOARD-2000 Series



Model OMB-DBK15

\$649



- ✓ Ideally Suited for 4 to 20 mA Measurements
- ✓ Can Measure up to ± 30 V*
- ✓ Provides 16 Differential Input Channels
- ✓ Offers User-Configurable Current or Voltage Input

Each OMB-DBK15 multiplexing input card provides sixteen channels of current or voltage input to OMEGA's OMB-LOGBOOK and OMB-DAQBOARD-2000 Series data acquisition systems.

An OMB-LOGBOOK or OMB-DAQBOARD-2000 Series can accept up to 16 OMB-DBK15 cards, for a total of 256 potential analog input channels per system.

The OMB-DBK15 features a 16-channel multiplexer and a programmable gain input amplifier. Its durable component sockets accept resistors that configure each channel for either current-to-voltage conversion or for voltage attenuation.

* ± 10 V to 30 V input signals can be measured by installing attenuation resistors on the card

The OMB-DBK15, \$649, universal current/voltage input card, shown smaller than actual size

The OMB-DBK15 is supplied with sixteen precision 250 ohm resistors for making 4 to 20 mA measurements, and sixteen sets of 6:1 voltage dividers for accommodating up to ± 30 V* inputs.

The OMB-DBK15 can also accept other, user-supplied resistor values, facilitating user-selectable current-to-voltage conversion or voltage attenuation factors.

When employed without resistors, the OMB-DBK15 provides sixteen differential voltage inputs, which accommodate ± 5 V full scale inputs.

The OMB-DBK15's input amplifier is software programmable for x1 or x2 gain per channel, and for unipolar 0 to +10 V or bipolar -5 to +5 V input per channel.

Voltage Measurements. The OMB-DBK15 accommodates voltage measurements beyond the standard 10 V range, accepting voltage divider resistors for up to ± 30 * VFS inputs. You can obtain any combination of input ranges by simply installing the appropriate resistor combination on the OMB-DBK15 card. The card's on-board programmable gain instrumentation amplifier (PGIA)

can be set for a ± 5 V output span or a 0 to +10 V output span, allowing users to set the OMB-LOGBOOK and OMB-DAQBOARD-2000 Series for either configuration.

Current Measurements.

The OMB-DBK15 is ideal for accommodating transducers with 4 to 20 mA output; one need only install the 250 ohm resistors provided in the appropriate location on the board.

SPECIFICATIONS

Connector: DB37 male, mates with P1 pinout on the OMB-LOGBOOK and OMB-DAQBOARD-2000 Series; screw-terminals provided for signal connection

Gain Ranges: x1, x2

Number of Channels: 16 differential
Voltage Input Ranges: 0 to +10 Vdc, ± 5 Vdc (less attenuating resistors)

Current Input Range: ± 20 mA max
Gain Accuracy: $\pm 0.05\%$ typ; $\pm 0.25\%$ max

Maximum Input Voltage (without damage): ± 35 Vdc

Cables: Use OMB-CA-37-x with OMB-LOGBOOK and OMB-DAQBOARD-2000 Series

AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)		
Model Number	Price	Description
OMB-DBK15	\$649	Universal Current/Voltage Input Card

Ordering Example: OMB-DBK15 universal current/voltage input card, \$649.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters