

## PR-13-Series

### RTD Probe with Large 3-Prong Connector

The PR-13 RTD probe assembly has a heavy duty 3-prong Omega "OTP" style connector for easy connection to extension cables, hand-held meters or other instrumentation. Probe diameter is 1/8", 3/16" or 1/4". The measuring portion of the probe can be simply inserted into a container to measure liquid temperature, or fixed into place in a pipe, tank, or vessel using an optional "BRLK" or "SSLK" compression fitting. These probes can be ordered with PT100 or PT1000 resistance element.



### Features

- Class A accuracy, conforming to IEC 60751
- Low temperature range: -50 to 250°C (-58 to 482°F)
- High temperature range: -50 to 450°C (-58 to 842°F)
- Extreme temperature range: -200 to 600°C (-328 to 1112°F)
- Standard probe lengths of 2, 3, 4, 6, 9, 12, 18, and 24"
- Resistance value: PT100 Ω or PT1000 Ω
- Integral male connector (female sold separately)
- Choice of PT100 and PT1000 Ω element
- IP67 Ingress Protection

### Specifications

Model	PR-13L (Low)	PR-13H (High)	PR-13E (Extreme)
Process Temperature Range	-50 to 250°C (-58 to 482°F)	-50 to 450°C (-58 to 842°F)	-200 to 600°C (-328 to 1112°F)
Accuracy	Class A	Class A	Class A from -100 to 450°C (-148 to 842°F); or else Class B
Nominal Resistance and Curve	100 Ω and 1000 Ω at 0°C standard; TCR = 0.00385 Ω/Ω/°C standard		
Connection Type	Large Connector	Large Connector	Large Connector
Dimensions	Diameters: 1/8, 3/16 and 1/4 inch. Standard probe length of 2, 3, 4, 6, 12, 18 and 24 inch. Other lengths may be built using our configurator.		
Ingress Protection	IP67	IP67	IP67
Response time T90 (s)	1/8" 0.75 sec 3/16" 0.975 sec 1/4" 1.2 sec	1/8" 1.00 sec 3/16" 1.55 sec 1/4" 2.10 sec	1/8" 1.5 sec 3/16" 1.95 sec 1/4" 2.4 sec
Vibration	IEC 60068-2-6; 5 to 2000 Hz sweep rate, one active per minute; number of sweep cycles 10 and acceleration 5g (15 probes tested together) Duration: 1 day		
Shock	IEC 60068-2-27; 50g/11ms (15 probes tested together) Duration: 1 day		